


CPDQT5V0SP-HF

RoHS Device
Halogen Free




Features

- IEC61000-4-2 Level 4 ESD protection.
- ESD Rating of Class 3 (>16kV) per Human Body Mode.
- Super low capacitance 0.5 pF
- Low clamping voltage.
- Small body outline dimensions:
0.039" x 0.024"(1.00mm*0.6mm)

Mechanical data

- Epoxy: Meets UL 94V-0
- Case: 0402/SOD-882 small outline plastic package.
Void-free, Transfer-molded, Thermosetting plastic.
- Lead finish: Ni-Pd-Au
- Mounting position: Any.
- High temperature soldering guaranteed: 260°C/10 second.

Circuit Diagram





Maximum Rating and Electrical Characteristics

(at $T_A=25^\circ\text{C}$ unless otherwise noted, $V_F=1.0\text{V}$ Max. @ $I_F=10\text{mA}$ for all types)


Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Working Peak Reverse Voltage		V_{RWM}			5.0	V
Breakdown voltage	$I_R = 1\text{mA}$	V_{BR}	5.4			V
Maximum reverse leakage current	$V_R = 5\text{V}$	I_R			1.0	μA
Junction capacitance	$V_R = 0\text{V}, f = 1\text{MHz}$	C_T		0.5	0.9	pF
ESD capability	IEC 61000-4-2(air)	ESD			15	kV
	IEC 61000-4-2(Contact)	ESD			10	kV
Clamping Voltage	$I_{PP} = 1\text{A}, t_p = 8/20\mu\text{s}$	V_c			12.9	V
Total power dissipation on FR-5 board (Note 1)	$T_A = 25^\circ\text{C}$	P_D			150	mW
Junction temperature		T_j	-55		125	$^\circ\text{C}$
Storage temperature		T_{STG}	-55		150	$^\circ\text{C}$

NOTES: 1. FR-5=1.0*0.75*0.62in.
2. V_{BR} is measured with a pulse test current I_R at an ambient temperature of 25°C .
3. Surge current waveform per Figure1.

RATING AND CHARACTERISTIC CURVES (CPDQT5V0SP-HF)



Reel Taping Specification




0402 (SOD-882)	SYMBOL	A	B	C	d	D	D ₁	D ₂
	(mm)	0.70 ± 0.05	1.12 ± 0.05	0.55 ± 0.05	1.50 + 0.10 - 0	178.00 Max.	50.00 Min.	13.00 ± 0.50
	(inch)	0.028 ± 0.002	0.044 ± 0.002	0.022 ± 0.002	0.059 + 0.004 - 0	7.008 Max.	1.969 Min.	0.512 ± 0.020

0402 (SOD-882)	SYMBOL	E	F	P	P ₀	P ₁	T	W	W
	(mm)	1.75 ± 0.10	3.50 ± 0.05	2.00 ± 0.05	4.00 ± 0.10	2.00 ± 0.05	0.229 ± 0.02	8.30 Max.	10.90 Max.
	(inch)	0.069 ± 0.004	0.138 ± 0.002	0.079 ± 0.002	0.157 ± 0.004	0.079 ± 0.002	0.009 + 0.001	0.327 Max.	0.429 Max.

Marking Code

Part Number	Marking Code
CPDQT5V0SP-HF	N




Month Code:

Month	Odd Year (per A.D.)	Even Year (per A.D.)
Jan	1	E
Feb	2	F
Wer	3	H
Apr	4	J
May	5	K
Jun	6	L

Month	Odd Year (per A.D.)	Even Year (per A.D.)
Jul	7	N
Aug	8	P
Sep	9	U
Oct	T	X
Nov	V	Y
Dec	C	Z

Suggested PAD Layout

SIZE	0402/SOD-882	
	(mm)	(inch)
A	0.70	0.035
B	0.40	0.012
C	0.70	0.016
D	1.10	0.047
E	0.30	0.024



Standard Packaging

Case Type	Qty Per Reel	Reel Size
	(Pcs)	(inch)
0402/SOD-882	10,000	7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[CPDQT5V0SP-HF](#)