



Fuse-link, high speed, 50 A, AC 240 V, DC 200 V, 100 kA, BS88, 18 x 59 mm, aR, BS

Part no. **50AMP 240V AC BS88 FUSE**
Catalog No. **GSA50**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	50
Rated voltage			AC 240 V DC 200 V
Construction size			BS88
Size			18 x 59 mm
Utilization category			aR
Breaking Capacity		kA	100
usable for size/applications			Protection of semi-conductor devices
Standard/Approval			BS
Shape			offset bolted tags
Standards/Regulations			BS88-4

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			Other
Type of current			
Rated voltage AC		V	
Rated voltage DC		V	
Rated current		A	50
Utilization category			aR (accompanied semiconductor protection)
Breaking capacity		kA	
Colour code			
Type of fuse status indicator			None
Power loss at rated current		W	
Mounting holes			
Centre-to-centre distance of connections		mm	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[GSA50](#)