

# +/-144VDC External Battery Pack for 208V SUT-Series UPS

MODEL NUMBER: BP288VEBP



External battery pack provides extended runtime for compatible 3-phase 208V Tripp Lite UPS systems.

## Features

**+/-144VDC External Battery Pack Gives Your Compatible UPS System Extended Runtime**The BP288VEBP is compatible only with 3-phase 208V SUT20K, SUT30K, SUT40K, SUT60K and other UPS systems that specify the use of this battery pack. Not only does it provide extended runtime, but it can also be daisy-chained to additional external battery packs for even longer extended-run operation. The three-pole input/output terminal blocks allow safe, simple hardwire installation, as well as internal disconnect for battery isolation.

**Rugged Steel Construction Designed to Last in Busy IT Applications**The steel cabinet features front and rear doors that provide easy access to the recyclable internal batteries and input/output terminal blocks. A 250A circuit breaker protects your equipment from dangerous overcurrent or overloads, while 63A fuses guard each battery string. Pre-installed rolling casters allow you to move the cabinet smoothly to its intended destination. Use the adjustable levelers for secure deployment on a stable surface.

**One-Year Warranty**The BP288VEBP is backed by a one-year warranty, ensuring reliability and performance.

## Highlights

- Connects to expandable 208V SUT-Series UPS systems for extended runtime
- Supports daisy-chaining to additional battery packs for even longer runtime
- Steel cabinet has front/rear doors for easy access to recyclable internal batteries
- 250A DC breaker protects equipment from potentially hazardous overcurrent
- Pre-installed metal casters allow you to smoothly roll the unit to its destination

## Applications

- Extend the runtime of your compatible Tripp Lite UPS system to maintain operation during all power conditions
- Daisy-chain to additional battery packs to provide even longer extended-run operation for backing up essential equipment

## System Requirements

- SUT20K, SUT30K, SUT40K, SUT60K or other UPS system specifying compatibility with this external battery pack

## Package Includes

- BP288VEBP +/-144VDC External Battery Pack for 208V SUT-Series UPS
- Owner's manual

# Specifications

| OVERVIEW           |              |
|--------------------|--------------|
| UPC Code           | 037332204110 |
| INPUT              |              |
| Input Phase        | 3-Phase      |
| BATTERY            |              |
| Expandable Runtime | Yes          |



Powering Business Worldwide



|                                                               |                                                                                                                             |
|---------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| DC System Voltage (VDC)                                       | +/- 144VDC                                                                                                                  |
| UPS Connection                                                | Hardwire (contractor supplies wiring - see Owner's Manual for gauge recommendations and complete installation instructions) |
| <b>PHYSICAL</b>                                               |                                                                                                                             |
| Material of Construction                                      | Steel                                                                                                                       |
| External Battery Pack Form Factor                             | Tower                                                                                                                       |
| Installation Form Factors Supported with Included Accessories | Tower                                                                                                                       |
| Shipping Dimensions (hwd / in.)                               | 30.12 x 26.77 x 37.40                                                                                                       |
| Shipping Dimensions (hwd / cm)                                | 76.50 x 68.00 x 95.00                                                                                                       |
| Shipping Weight (lbs.)                                        | 871.00                                                                                                                      |
| Shipping Weight (kg)                                          | 395.08                                                                                                                      |
| Unit Dimensions (hwd / in.)                                   | 23.500 x 30.080 x 33.580                                                                                                    |
| Unit Dimensions (hwd / cm)                                    | 199.9 x 101.6 x 74.9                                                                                                        |
| Unit Weight (lbs.)                                            | 771.62                                                                                                                      |
| Unit Weight (kg)                                              | 350.00                                                                                                                      |
| <b>STANDARDS &amp; COMPLIANCE</b>                             |                                                                                                                             |
| Product Compliance                                            | RoHS                                                                                                                        |
| <b>WARRANTY &amp; SUPPORT</b>                                 |                                                                                                                             |
| Product Warranty Period (Worldwide)                           | 1-year limited warranty                                                                                                     |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[BP288VEBP](#)