

HMR


1/4" x 1 1/4" Panel mount fuseholder




Product features

- For 1/4" diameter x 1 1/4" fuses
- IP67 rating for exposed locations
- Prevents radio frequency interference
- Provides both shielding and grounding

Dimensions—mm



Punched Mounting Hole



Product specifications

Knob	Bayonet type
Terminals	Solder lug
Enclosure	IP67 rated for exposed locations when shielding cap is secured
Panel thickness	0.188 max.
Rating	30 A, 250 V
Body and knob molding material	SDG-F per Mil-M-14, light grey, Diallyl Phthalate
Mechanical shock	MIL-STD-202, Method 213, Method II
Terminal strength	5 lbs
Torque	Mounting-20 in-lbs
Shield continuity	With fuseholder mounted normally and shield cap in place, electrical resistance from shield to cap to mounting panel not to exceed 0.5 ohms.

Ordering

- HMR: (10 parts in a carton)
- BK-HMR: (50 parts parts per carton)

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
www.eaton.com/electronics

© 2017 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. 10689 BU-MC17035
 July 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[BK/HMR](#) [HMR](#)