

PTSLR0603

Low resistance SMD PTC fuses



Product features

- Positive temperature coefficient (PTC)
- Surface mount resettable fuse
- Low resistance
- Compact 0603 (1608 metric) footprint
- Voltage rating 6 V to 8 V
- Current rating from 0.5 A to 3.0 A
- Fast time-to-trip

Applications

- Data ports
- Micromotors and fans
- Low voltage test and measurement
- Low voltage hand held equipment
- Mobile devices
- PC-based medical equipment
- USB protection
- Secondary Li-ion battery protection
- Game consoles, set top boxes
- Battery charging & charging connections

Agency information

- cURus Recognized file no. E343021
- TUV: File R 50506608



Environmental compliance



Part number system/ordering:

PTSLR06038V050

- PT= PTC resettable fuse
- S= Surface mount
- LR = Low resistance
- 0603= Dimension code
- 8V= Maximum voltage
- 050= Ihold current rating (050= 0.5 A)



Powering Business Worldwide

Product specifications

	V _{max} ¹	I _{max} ²	I _{hold} ³	I _{trip} ⁴	P _d ⁵	Time-to-trip (maximum)		Resistance ⁶		Safety approvals	
Part number	(V _{dc})	(A)	(A)	(A)	typical (W)	(A)	(seconds)	Initial (R _i) minimum (Ω)	Post trip (R _t) maximum (Ω)	cURus	TUV
PTSLR06038V050	8	25	0.50	1.0	0.5	8	0.6	0.050	0.40	✓	-
PTSLR06038V075	8	25	0.75	1.5	0.5	8	1	0.030	0.165	✓	-
PTSLR06038V100	8	25	1.00	2.0	0.5	8	2	0.030	0.15	✓	-
PTSLR06036V125	6	50	1.25	2.5	0.5	8	3	0.025	0.14	✓	✓
PTSLR06036V150	6	50	1.50	3.0	0.5	8	4	0.020	0.12	✓	✓
PTSLR06036V175	6	50	1.75	3.5	0.5	8	5	0.008	0.07	✓	✓
PTSLR06036V200	6	50	2.00	4.0	0.5	8	5	0.008	0.065	✓	✓
PTSLR06036V250	6	50	2.50	5.0	0.5	8	5	0.008	0.06	✓	✓
PTSLR06036V300	6	50	3.00	6.0	0.5	8	5	0.008	0.05	✓	✓

1. V_{max}: Maximum continuous voltage the device can withstand without damage at rated current

2. I_{max}: Maximum fault current the device can withstand without damage at rated voltage

3. I_{hold}: Maximum current the device will pass without interruption at +23 °C still air


4. I_{trip}: Minimum current that will transition the device from low resistance to high resistance at +23 °C still air

5. P_d: Power dissipated from the device when in tripped state at +23 °C still air

6. R_i: Minimum resistance of the device at +23 °C


R_t: Maximum resistance of the device one hour after tripping at +23 °C

Dimensions—mm



No part marking

Recommended pad layout




Part number	A max	B max	C max	D min	F	G	H
PTSLR06038V050	1.80	1.00	0.75	0.15	0.8	0.6	0.8
PTSLR06038V075	1.80	1.00	1.00	0.15	0.8	0.6	0.8
PTSLR06038V100	1.80	1.00	1.00	0.15	0.8	0.6	0.8
PTSLR06036V125	1.80	1.00	1.00	0.15	0.8	0.6	0.8
PTSLR06036V150	1.80	1.00	1.00	0.15	0.8	0.6	0.8
PTSLR06036V175	1.80	1.00	1.00	0.15	0.8	0.6	0.8
PTSLR06036V200	1.80	1.00	1.10	0.15	0.8	0.6	0.8
PTSLR06036V250	1.80	1.00	1.10	0.15	0.8	0.6	0.8
PTSLR06036V300	1.80	1.00	1.10	0.15	0.8	0.6	0.8

General specifications

Operating temperature: -40 °C to + 85 °C (with derating)
Storage temperature: -10 °C to + 40 °C
Storage relative humidity: ≤70%
Storage condition: Keep away from corrosive atmosphere and sunlight
Passive aging: IEC60738-1, +60 °C/90% RH, 168 hours, ≤3*R1max
Humidity aging: +85 °C, 85% RH, 96 hours, ≤3*R1max
Thermal shock: IEC60738-1, +85 °C/ -40 °C, 20 cycles, ≤3*R1max
Trip cycle life: UL1434, Vmax, Imax, 100 cycles, no arcing or burning
Trip endurance: UL1434, Vmax, Itrip ≤ I ≤ Imax, 2 hours, no arcing or burning
Solvent resistance: Freon, Trichloroethane, Hydrocarbons: no change
MSL test: J-STD-020, MSL=2, pass and no visible damage


Thermal derating curve PTSLR0603



Packaging information

PTSLR06038V050, PTSLR06038V075, PTSLR06038V100, PTSLR06036V125, PTSLR06036V150
Supplied in tape and reel packaging, 5000 parts per 7.0" (178 mm) diameter reel (EIA-481 compliant)

PTSLR06036V175, PTSLR06036V200, PTSLR06036V250, PTSLR06036V300
Supplied in tape and reel packaging, 3000 parts per 7.0" (178 mm) diameter reel (EIA-481 compliant)




PTSLR06038V050, PTSLR06038V075, PTSLR06038V100, PTSLR06036V125,

W	F	E1	E2	P0	P1	P2	D0	D1	A0	B0	K0	T
8.00 ± 0.30	3.50 ± 0.10	1.75 ± 0.10	-	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	1.50 + 0.10/-0	-	1.10 ± 0.10	1.85 ± 0.10	0.60 ± 0.10	0.20 ± 0.05

PTSLR06036V150, PTSLR06036V175, PTSLR06036V200, PTSLR06036V250, PTSLR06036V300

W	F	E1	E2	P0	P1	P2	D0	D1	A0	B0	K0	T
8.00 ± 0.30	3.50 ± 0.10	1.75 ± 0.10	-	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05	1.50 + 0.10/-0	-	1.10 ± 0.10	1.85 ± 0.10	0.85 ± 0.10	0.20 ± 0.05

Wave solder profile



Reference EN 61760-1:2006

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat		
• Temperature min. (T_{smin})	100 °C	100 °C
• Temperature typ. (T_{styp})	120 °C	120 °C
• Temperature max. (T_{smax})	130 °C	130 °C
• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds
Δ preheat to max Temperature	150 °C max.	150 °C max.
Peak temperature (T_p)*	235 °C – 260 °C	250 °C – 260 °C
Time at peak temperature (t_p)	10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave
Ramp-down rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max
Time 25°C to 25°C	4 minutes	4 minutes

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended

Solder reflow profile




Table 1 - Standard SnPb solder (T_c)

Package thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5 mm	235 °C	220 °C
≥ 2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) Free Solder (T_c)

Package thickness	Volume mm^3 <350	Volume mm^3 350 - 2000	Volume mm^3 >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L) Time (t_L) maintained above T_L	183 °C 60-150 seconds	217 °C 60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_c)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2021 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1047 BU-ELX21047
June 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[PTSLR06036V125](#) [PTSLR06036V150](#) [PTSLR06036V175](#) [PTSLR06036V200](#) [PTSLR06036V250](#)
[PTSLR06036V300](#) [PTSLR06038V050](#) [PTSLR06038V075](#) [PTSLR06038V100](#)