


STS232712B451

TVS Diode array ESD suppressor



Product features

- 400 watts peak pulse power per line ($t_P = 8/20 \mu s$)
- Protects two 7 V to 12 V lines
- Low clamping voltage
- Low capacitance
- Solid-state silicon avalanche technology
- Meets moisture sensitivity level (MSL) 3
- Molding compound flammability rating: UL 94V-0
- Termination finish: Tin

Applications

- Protection of RS-485 transceivers with extended common-mode range
- Security systems
- Automatic teller machines
- HFC systems
- Networks

Environmental compliance and general specifications


- IEC61000-4-2 (ESD)
 - ± 15 kV (air)
 - ± 8 kV (contact)
- IEC61000-4-5 (Lightning) 12 A (8/20 μs)



Ordering part number

	ST	S23	2	712	B	451
Family	_____	_____	_____	_____	_____	_____
Package (S23- SOT23)	_____	_____	_____	_____	_____	_____
Number of channels (2-2)	_____	_____	_____	_____	_____	_____
Operating voltage (712-7 V/12 V)	_____	_____	_____	_____	_____	_____
Bi/Uni directional (B- Bi)	_____	_____	_____	_____	_____	_____
Capacitance (451- 45 pF)	_____	_____	_____	_____	_____	_____

Pin out/functional diagram



Powering Business Worldwide

Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

STS232712B451

Parameter	Symbol	Value	Unit
Peak pulse power dissipation on 8/20 μs waveform	P_{PP}	400	W
ESD per IEC 61000-4-2 (Air)	V_{ESD}	+/-15	kV
ESD per IEC 61000-4-2 (Contact)		+/-8	
Lead soldering temperature	T_L	+260 (10 seconds)	°C
Operating junction temperature range	T_J	-55 to +125	°C
Storage temperature range	T_{STG}	-55 to +150	°C

Electrical characteristics

(+25 °C)


Pins 1, Pin 2 to Pin 3 (12 V TVS)

Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse stand-off voltage	-	-	-	12	V_{RWM} (V)
Reverse breakdown voltage	$I_T = 1$ mA	13.3	-	-	V_{BR} (V)
Reverse leakage current	$V_R = V_{RWM}$	-	-	1	I_R (μA)
Clamping voltage	$I_{PP} = 5$ A, $t_p = 8/20$ μs	-	20	23	V_C (V)
	$I_{PP} = 12$ A, $t_p = 8/20$ μs	-	23	26	
Junction capacitance	$V_R = 0$ V, $f = 1$ MHz	-	-	75	C_J (pF)
	$V_R = V_{RWM}$, $f = 1$ MHz	-	45	-	

Pins 3, Pin 1 to Pin 2 (7 V TVS)


Parameter	Test condition	Minimum	Typical	Maximum	Symbol (Units)
Reverse stand-off voltage	-	-	-	7	V_{RWM} (V)
Reverse breakdown voltage	$I_T = 1$ mA	7.5	-	-	V_{BR} (V)
Reverse leakage current	$V_R = V_{RWM}$	-	-	1	I_R (μA)
Clamping voltage	$I_{PP} = 5$ A, $t_p = 8/20$ μs	-	12	15	V_C (V)
	$I_{PP} = 12$ A, $t_p = 8/20$ μs	-	15	18	
Junction capacitance	$V_R = 0$ V, $f = 1$ MHz	-	-	75	C_J (pF)
	$V_R = V_{RWM}$, $f = 1$ MHz	-	45	-	

Mechanical parameters, pad layout- mm/inches




Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.9	1.15	0.035	0.045
A1	0.00	0.10	0.000	0.004
b	0.25	0.325	0.010	0.013
C	0.22	0.25	0.009	0.01
D	2.8	3.0	0.11	0.118
e	1.8	1.9	0.071	0.075
E	1.2	1.4	0.047	0.055
L	0.30	0.50	0.012	0.02
He	2.25	2.55	0.089	0.1
X	0.8		0.0315	
X1	0.95		0.037	
Y	0.80		0.0315	
Z	2.02		0.0795	

Part marking



Packaging information mm/inches


Drawing not to scale.
Supplied in tape and reel packaging, 3,000 parts per 7" diameter reel (EIA-481 compliant)




Symbol	Millimeter	Inches
	Typ.	Typ.
A	3.15	0.124
B	2.77	0.109
C	1.22	0.048
d	Φ1.50	Φ0.059
E	1.75	0.069
F	3.50	0.138
P0	4.00	0.157
P	4.00	0.157
P1	2.00	0.079
W	8.00	0.315
D	Φ178	Φ7.008
D1	54.40	2.142
D2	13.00	0.512
G	R78.00	R3.071
H	R25.60	R1.008
I	R6.50	R0.256
W1	9.50	0.374
W2	12.30	0.484

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)


V- I curve characteristics (Bi-directional)




Pulse waveform (8/20 μ s)



Pulse derating curve



ESD waveform



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11157 BU-MC20139
September 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[STS232712B451](#)