



PLUG CONTACT: 131□14019X


SOCKET CONTACT: 132□14019X

(c) SHOULD BE USED FOR
D-SUB COMBINATION
MALE CONNECTORS

(c) SHOULD BE USED FOR
D-SUB COMBINATION
FEMALE CONNECTORS




INSTALLATION DIMENSION



RoHS compliant

STRIPPING
DIMENSIONS



(c) (b) NOTES:

1. INSULATOR:
PLUG CONTACT: PTFE, BLUE
SOCKET CONTACT: PTFE, WHITE
2. CONTACT: COPPER ALLOY,
PLATING CONTACT AREA:
□ = A: GOLD FLASH OVER NICKEL
□ = J: 50 µin HARD GOLD OVER NICKEL
3. SOLDER CUP ACCEPTS CABLE AWG 20
4. RETAINING RING: COPPER ALLOY, NICKEL PLATED
5. PLUG CONTACT MAY ONLY BE MOUNTED IN
D-SUB COMBINATION MALE CONNECTORS,
SOCKET CONTACT MAY ONLY BE MOUNTED IN
D-SUB COMBINATION FEMALE CONNECTORS

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm
3 x c	Ä21-007	21.01.2021	JLE	date	name	
1 x b	Ä3527	14.12.2009	Henneb.	drawn 07.05.2002	Parei	
a	Original			appd. 07.05.2002	E. Mickenbecker	
rev.	description	date	name	norm		
				d-old		

CONEC®

scale:	4:1
material:	SEE NOTES
title:	HIGH VOLTAGE PLUG + SOCKET CONTACT solder termination straight for D-SUB COMBINATION CONNECTORS
dwg no:	13K1A568
part no:	SEE DRAWING
	DIN-A4 sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131J14019X](#)