




② STRIPPING DIMENSIONS



② ASSEMBLY TOOLING:

1. CENTER CONTACT:
SOLDERED
2. OUTER CONDUCTOR:
SOLDERED OR CRIMPED
USE CRIMP TOOL: 360X10519X
WITH TOOL INSERT: 360X11019X
INSERT CAVITY C: HEX 2.67/105



②

Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos. 4/5
132J20019X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
132A20019X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance ISO 2768-c	dim. in mm
				date	name
				drawn 10.02.06	Lehmenkühler
				appd. 10.02.06	Mickenbecker
				norm	
				d-old	
9 x b	A5173	17.04.14	HS	CONEC	
a	Original				
rev.	description	date	name		

scale:	8:1
material:	COPPER ALLOY (Pos. 1 - 5)
title:	COAXIAL CONTACT SOCKET 50 OHM center contact solder, outer contact solder/crimp for cable RG 178 B/U, 196 A/U, 404/U
dwg no:	13K2IR3A
part no:	see table
DIN-A3	sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[132J20019X](#)