





used for: D-SUB COMBINATION



NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. FRAME: STEEL, NICKEL PLATED
4. FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
5. RIVETED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. CONNECTOR IS PART MARKED: 3025W3PXX99S90A CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

Customer Specific Product			
2007	date	name	
drawn	24.10.	Lehmenkühler	
appd.	24.10.	Mickenbecker	
norm			
d-old			
a	Origin		
rev.	description	date	name

tolerance	
dim. in mm	
2007	
drawn	
appd.	
norm	
d-old	
a	
rev.	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB COMBINATION MALE 25W3P CRIMP STYLE with frame, float mount for blind mating system
dwg no:	AutoCAD 2006
part no:	13K1A2317
sh:	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

3025W3P XK99S90A