








No. of pos.	A -0,76	B +0,25	C	D -0,3
9	31,19	16,79	25,00 ^{+0.12} _{-0.10}	6,12
15	39,52	25,12	33,30 ^{+0.15}	6,12
25	53,42	38,84	47,04 ± 0.13	5,99
37	69,70	55,30	63,50 ^{+0.13} _{-0.11}	5,99

Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

- METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- JACKSCREW: STAINLESS STEEL 1.4305
- WIRE ROPE: STAINLESS STEEL 1.4401
- RETAINING WASHER: STAINLESS STEEL 1.4122
- TERMINAL RING: UNINSULATED, COPPER ALLOY; min. 200µinTIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
- CONNECTOR IS PART MARKED: **PART NO. CONEC ABC**

Part No. for socket connector		
No. of pos.	UNC 4-40	M 3
9	16-000280	16-000230
15	16-000290	16-000240
25	16-000300	16-000250
37	16-000310	16-000260

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND				tolerance	dim. in mm	
				ISO 2768-m	date	name
1 x b	Ä 3186	17.11.2008	Petker		drawn	30.04.08 Sonnenberg
a	Origin				appd.	30.04.08 Fischer
rev.	description	date	name		norm	
					d-old	

scale:	2:1 (5:1)	
material:	SEE NOTES	
title:	SCREEN CAP 9-37pos. FOR SOCKET CONNECTOR with threaded insert, jackscrew and wire rope	
dwg no:	Inventor 10	DIN-A3
	16K1A2276	sh: 1
part no:	see table	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[16-000300](#) [16-000280](#) [16-000290](#) [16-000310](#)