






P.C.B. HOLE DRILLINGS




(b)

4,1

NOMINAL BEFORE
INSTALLATION




SEE NOTE 12



NOTES:

1. RoHS COMPLIANT
2. SUITABLE FOR WAVESOLDERING
3. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
4. INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
5. CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
CONTACT TAILS PRETINNED
6. MOUNTING BRACKET: PBT GF UL 94 V-0; BLACK
7. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. GROUNDING-CLIP: COPPER ALLOY
PCB-HOLE: $\phi 3,1 \pm 0,1$; PCB THICKNESS 1,6mm
9. CAPACITANCE: 1300pF $\pm 20\%$
10. DIELECTRIC WITHSTANDING VOLTAGE: 424 VDC
11. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
12. CONNECTOR IS PART MARKED: [242A12860X CONEC ABC]



Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			
DO NOT ALTER CAD DRAWING BY HAND			
2 x b	A 2772	15.08.07	Lehm.
a	Origin		
rev.	description	date	name

tolerance		dim. in mm	
date	name		
drawn	01.03.96	Barcinski	
appd.	01.03.96	Mickenbecker	
norm	DIN 41652		
d-old			

scale: 2:1 (5:1)	
material: SEE NOTES	
title: D-SUB FILTER FEMALE 90° 9pos. SOLDER PIN ANGLED 0.370inch threaded insert, mounting bracket, grounding clip	
dwg no:	Inventor 10 (b) DIN-A3
16K11U1A	
sh: 1	
part no:	242A12860X

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[242A12860X](#)