



FEATURES


Small Size - High Voltage - General Purpose

APPLICATIONS

General Purpose - Bypass - Coupling - Blocking

Operating Temperature Range	-40°C to +105°C					
Capacitance Tolerance	±10% at 1 kHz, 25°C +5% optional					
Peak, AC voltage (50/60 Hz)	WVDC	100	250	400	630	
	VAC	63	160	200	220	
	For T>+85°C , The voltage must be decreased by 1.25% per °C					
Dissipation Factor (MAX) 25°C	Frequency (kHz)		Dissipation Factor			
	1		1.0%			
	10		1.5%			
Insulation Resistance @25°C (<70% RH) for 1 minute at 100VDC applied	Capacitance		Insulation Resistance			
	<0.33µF		9000 MΩ			
	>0.33µF		3000 MΩxµF			
Load Life	2000 Hours, +85C with 125% of rated voltage					
	Capacitance Change			<5% of initially measured value		
	Dissipation Factor			<0.005 at 1kHz and 25°C		
	Insulation Resistance			≥50% of maximum specified value		
Damp Heat test	1000 Hours, 93%RH (+/-2%), +40°C and no voltage applied					
	Capacitance Change			<5% of initially measured value		
	Dissipation Factor			<0.005 at 1kHz and 25°C		
	Insulation Resistance			≥50% of maximum specified value		
Self Inductance	<1 nano-Henry per mm of body length and lead length					
Capacitance Drift Factor	<1.0% after 2 years at 40°C					
Capacitance Temperature Coefficient	+400 ppm/°C, ±200ppm/°C					
Dielectric Strength	Terminal to Terminal					
	160% of VDC applied for 2 Seconds and 25°C					
Dielectric	Polyester					
Construction	Metallized film					
Coating	Flame Retardant epoxy resin (UL94V0)					
Leads	Lead free Tinned Leads					

Special Order Options



L MAX	10.5	12	18.5	26	31
S+1.0	7.5	10	15	22.5	27.5
G MAX	1.5	1.5	1.5	1.5	1.5
d +0.05	0.6	0.6	0.8	0.8	0.8

MMR

Small Size Epoxy Dipped
Metallized Polyester Radial
Lead

WVDC	Capacitance (μF)	IC PART NUMBER	dv/dt (v/μ sec.)	Dims LxHxT (mm)	S (MM)	d (MM)
100	0.15	154MMR100K	35	10.3x7.5x4.5	7.5	0.6
100	0.22	224MMR100K	35	10.3x8x5	7.5	0.6
100	0.33	334MMR100K	35	10.3x10.7x6	7.5	0.6
100	0.68	684MMR100K	30	12x13x6	10	0.6
100	1	105MMR100K	30	12x14x6.7	10	0.6
100	1.5	155MMR100K	20	18.5x13.4x6	15	0.8
100	2.2	225MMR100K	20	18.5x15x7	15	0.8
100	3.3	335MMR100K	20	18.5x16.5x8.5	15	0.8
100	4.7	475MMR100K	10	26x17x7.5	22.5	0.8
100	5.6	565MMR100K	10	26x18.5x8.3	22.5	0.8
100	6.8	685MMR100K	10	26x18.5x9	22.5	0.8
100	8.2	825MMR100K	10	26x21x10	22.5	0.8
100	10	106MMR100K	10	26x21x11.5	22.5	0.8
250	0.01	103MMR250K	80	10.3x7.5x4.3	7.5	0.6
250	0.015	153MMR250K	80	10.3x7.5x4.4	7.5	0.6
250	0.022	223MMR250K	80	10.3x7.5x4.4	7.5	0.6
250	0.033	333MMR250K	80	10.3x7.5x4.5	7.5	0.6
250	0.047	473MMR250K	80	10.3x7.5x4.5	7.5	0.6
250	0.068	683MMR250K	80	10.3x7.5x4.5	7.5	0.6
250	0.1	104MMR250K	80	10.3x8.4x5.8	7.5	0.6
250	0.15	154MMR250K	80	10.3x10.8x6	7.5	0.6
250	0.22	224MMR250K	110	12x10.5x5.5	10	0.6
250	0.33	334MMR250K	110	12x12x6.5	10	0.6
250	0.47	474MMR250K	45	18.5x12.5x5.3	15	0.8
250	0.68	684MMR250K	45	18.5x13.5x6	15	0.8
250	1	105MMR250K	45	18.5x15x7.4	15	0.8
250	1.5	155MMR250K	45	18.5x16.8x9	15	0.8
250	2.2	225MMR250K	20	26x16.3x8.5	22.5	0.8
250	3.3	335MMR250K	20	26x18x10.3	22.5	0.8
250	4.7	475MMR250K	20	26x21.5x12	22.5	0.8
250	5.6	565MMR250K	15	31x22x11.8	27.5	0.8
250	6.8	685MMR250K	15	31x22.4x13	27.5	0.8

WVDC	Capacitance (μF)	IC PART NUMBER	dv/dt (v/μ sec.)	Dims LxHxT (mm)	S (MM)	d (MM)
250	8.2	825MMR250K	15	31x24.5x14.3	27.5	0.8
250	10	106MMR250K	15	31x25.8x15.9	27.5	0.8
400	0.01	103MMR400K	190	10.3x7.4x4.3	7.5	0.6
400	0.015	153MMR400K	190	10.3x7.5x4.4	7.5	0.6
400	0.022	223MMR400K	190	10.3x7.9x4.8	7.5	0.6
400	0.033	333MMR400K	190	10.3x9x6	7.5	0.6
400	0.047	473MMR400K	160	12x8.3x5	10	0.6
400	0.068	683MMR400K	160	12x10.5x5.4	10	0.6
400	0.1	104MMR400K	160	12x12x6.3	10	0.6
400	0.15	154MMR400K	65	18.5x12.4x5	15	0.8
400	0.22	224MMR400K	65	18.5x13x5.9	15	0.8
400	0.33	334MMR400K	65	18.5x14.9x7	15	0.8
400	0.47	474MMR400K	65	18.5x17x7.8	15	0.8
400	0.68	684MMR400K	30	26x16.5x7	22.5	0.8
400	1	105MMR400K	30	26x18x8.5	22.5	0.8
400	1.5	155MMR400K	25	31x19x9.5	27.5	0.8
400	2.2	225MMR400K	25	31x22x11	27.5	0.8
630	0.01	103MMR630K	200	12x7.5x4.5	10	0.6
630	0.015	153MMR630K	200	12x8.2x5	10	0.6
630	0.022	223MMR630K	200	12x10.5x5.3	10	0.6
630	0.033	333MMR630K	200	12x11.9x6	10	0.6
630	0.047	473MMR630K	200	12x13.5x6.5	10	0.6
630	0.068	683MMR630K	90	18.5x11x5.8	15	0.8
630	0.1	104MMR630K	90	18.5x14x6.3	15	0.8
630	0.15	154MMR630K	90	18.5x15.4x7.5	15	0.8
630	0.22	224MMR630K	90	18.5x16.5x9	15	0.8
630	0.33	334MMR630K	35	26x17x7.8	22.5	0.8
630	0.47	474MMR630K	35	26x18.5x9.3	22.5	0.8
630	0.68	684MMR630K	35	26x21x11.5	22.5	0.8
630	1	105MMR630K	30	31x21.9x12.5	27.5	0.8
630	1.5	155MMR630K	30	31x24.7x15.3	27.5	0.8
630	2.2	225MMR630K	30	31x29x19.5	27.5	0.8

Americas / EU
Phone: 1-508-996-8561
Email: cdena@cde.com



Asia
Phone: 852-2793-0931
Email: cdeasia@cde.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier / Knowles:](#)

103MMR630K	104MMR630K	104MMR250K	155MMR250K	225MMR400K	335MMR250K	224MMR400K
224MMR250K	103MMR400K	685MMR100K	104MMR400K	474MMR400K	105MMR630K	224MMR630K
105MMR250K	155MMR630K	474MMR250K	106MMR250K	223MMR400K	106MMR100K	475MMR250K
685MMR250K	334MMR250K	223MMR630K	683MMR400K	683MMR250K	153MMR250K	155MMR100K
334MMR400K	225MMR250K	154MMR250K	473MMR630K	105MMR400K	684MMR630K	105MMR100K
334MMR630K	473MMR400K	474MMR630KG	474MMR630K	153MMR630K	154MMR400K	333MMR250K
333MMR400K	155MMR400K	223MMR250K	475MMR100K	225MMR630K	225MMR100K	153MMR400K
683MMR630K	684MMR250K	333MMR630K	335MMR100K	684MMR400K	154MMR630K	473MMR250K
104MMR630KSA02	154MMR630KSA02	223MMR630KLL24	334MMR630KCB45	565MMR100K	825MMR100K	
565MMR250K	684MMR100K	224MMR100K	334MMR100K	825MMR250K	154MMR100K	