




FEATURES

High Voltage

APPLICATIONS

Voltage Multipliers - Medical Equipment

Operating Temperature Range	-40°C to +105°C				
Capacitance Tolerance	±10% at 1 kHz, 25°C ±5% optional				
Peak, AC voltage (50/60 Hz)	WVDC	2500	4000	6300	10000
	VAC	500	750	1000	1200
Dissipation Factor (MAX) 25°C	For T>+85°C , The voltage must be decreased by 1.25% per °C				
	Frequency (kHz)		C<0.1uF		0.1uF<C<1.0uF
	1		0.8%		0.8%
	10		1.5%		1.5%
	100		3.0%		-
Insulation Resistance @25°C (<70% RH)for 1 minute at 100VDC applied	Insulation Resistance				
	15000 MΩ				
Load Life	2000 Hours, +85C with 125% of rated voltage				
	Capacitance Change			≤5% of initially measured value	
	Dissipation Factor			≤0.00 at 1kHz and 25°C	
	Insulation Resistance			≥50% of maximum specified value	
Damp Heat test	56 days at40°C with 93%RH(+/-2%), +40°C and no voltage applied				
	Capacitance Change			≤5% of initially measured value	
	Dissipation Factor			≤0.005 at 1kHz and 25°C	
	Insulation Resistance			≥50% of maximum specified value	
Self Inductance	<1 nano-Henry per mm of body length and lead length				
Capacitance Drift Factor	<1.0% after 2 years at 40°C				
Capacitance Temperature Coefficient	+400 ppm/°C, ±200ppm/°C				
Dielectric Strength	Terminal to Terminal				
	160% of VDC applied for 2 Seconds and 25°C				
Dielectric	Polyester				
Construction	Metallized film Internal series connected				
Coating	Flame Retardant Polyester tape wrap (UL 510) with epoxy resin end fills(UL94V0)				
Leads	Lead free tinned copper leads				



Lead Diameter	
D	d
≤8	0.6
8<D≤22	0.8
>22	1.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier / Knowles:](#)

[104MWS402KN](#) [104MWS252KO](#) [152MWS103KT](#) [103MWS103KT](#) [153MWS103KT](#) [152MWS402KG](#)
[152MWS632KL](#) [222MWS103KT](#) [222MWS402KG](#) [222MWS632KL](#) [332MWS103KT](#) [332MWS402KG](#) [332MWS632KL](#)
[472MWS103KT](#) [472MWS252KG](#) [472MWS402KG](#) [472MWS632KL](#) [682MWS103KT](#) [682MWS252KG](#)
[103MWS402KG](#) [103MWS632KO](#) [153MWS252KG](#) [223MWS252KG](#) [223MWS402KJ](#) [223MWS632KO](#)
[333MWS402KJ](#) [333MWS632KO](#) [473MWS252KJ](#) [473MWS402KN](#) [473MWS632KO](#) [683MWS402KN](#) [224MWS252KO](#)
[334MWS252KO](#) [474MWS252KO](#)