



NOTES:

- METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- NO CONTACTS ON POS. A1 and A2
- UL APPROVED UNDER E228329
- CONNECTOR IS PART MARKED: 3007W2PCM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance				 dim. in mm		scale: 2:1 (5:1)			
										material: SEE NOTES			
				DO NOT ALTER CAD DRAWING BY HAND				date		name		title: D-SUB COMBINATION MALE 7W2P SOLDER CUP	
								drawn 08.05.02		Parei			
appd. 08.05.02		E.Mickenbecker											
norm													
3 x c		Ã3935		15.03.2011		K.H.		d-old		dwg no: Inventor 10		DIN-A3 sh: 1	
1 x b		Ã3231		19.12.2008		Lehmen							
a		Origin								13K1A562			
rev.		description		date		name				part no: 3007W2PCM99A10X			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3007W2PCM99A10X](#)