


1. METAL SHELLS: STEEL; min. 320μ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30μ" HARD GOLD OVER min. 50μ" NICKEL
4. HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING: 30μ" HARD GOLD OVER min. 50μ" NICKEL
5. METAL BRACKET: STEEL; min. 320μ" TIN over 80μ" NICKEL
6. THREADED INSERT: COPPER ALLOY; min. 200μ" TIN over 80μ" NICKEL
7. PCB-SNAP: COPPER ALLOY; min. 200μ" TIN over 80μ" NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
8. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
9. CONNECTOR IS PART MARKED: 3007W2SCT56N40X CONEC ABC
10. = CHECK DIMENSION

**Directive 2002/95/EC
„RoHS“
Compliant**

APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name



scale:		2:1 (5:1)	
material:		SEE NOTES	
title:			
D-SUB COMBINATION FEMALE 90°			
7W2S			
with threaded insert, metal bracket and clip			
dwg no:		AutoCAD 2004	DIN-A
13K2A1141			3
			sh: 1/1
part no: 3007W2SCT56N40X			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3007W2SCT56N40X](#)