






NOTES:

CRIMPING:

USE CRIMP TOOL: 360X10409X

WITH TOOL INSERT: 360X20029X


SELECTOR SETTINGS: 7 FOR AWG 10

6 FOR AWG 12

(b)

plating	part no.
GOLD FLASH over NICKEL	131A11039X
30µin HARD GOLD over min. 50µin NICKEL	131C11039X
50µin HARD GOLD over min. 50µin NICKEL	131J11039X

STRIPPING DIMENSIONS



3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
1	1	MATING SIDE	COPPER ALLOY	see table
pos	qty	description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			tolerance	scale: 8:1
			dim. in mm	material: see partlist
			drawn 12.07.12 Schmidt	title: HIGH POWER CONTACT MALE CRIMP VERSION 30A FOR AWG 10-12 D-SUB COMBINATION
			appd. 12.07.12 Koch	
			norm	
DO NOT ALTER CAD DRAWING BY HAND			d-old 13K1ID3A / 13K2ID3A	dwg no:
			1 x b A4380 12.07.12 HS	DIN-A3
rev.	description	date	name	sh: 1
a	Original			
			part no: see table	

Directive 2002/95/EC RoHS compliant

CONEC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131J11039X](#)