





Ø1,12 (25x)



1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY; PLATING (SEE PART NO.):
 - ☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
 - ☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
 - ☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
 - ☐ PLEASE ADD J for 50µin HARD GOLD over min. 50µin NICKELSOLDER CUP ACCEPTS CABLE AWG 20
4. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
7. CONNECTOR IS PART MARKED: 163□11289X CONEC ABC (see note 3)

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm		scale: 2:1 (5:1)			
								material: SEE NOTES			
				DO NOT ALTER CAD DRAWING BY HAND						title: D-SUB MALE 25pos. SOLDER CUP with threaded insert	
				date	name		dwg no: 16K1A3740 part no: 163□11289X (see note 3)				
				drawn 05.01.16	Lehmenkühler						
				appd. 06.01.16	Schmidt						
				norm							
				d-old	16K1A674 / 16K1A1739		DIN-A3				
2 x b	Ä5920	05.01.2016	Lehm.			sh: 1					
a	Original										
rev.	description	date	name								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A11289X](#)