





NOTES:

- METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY; PLATING (SEE PART NO.):
□ PLEASE ADD 1 for 30µm HARD GOLD over min. 50µm NICKEL
□ PLEASE ADD 3 for GOLD FLASH over NICKEL
- SNAP-LOCK AND SPACER CLIPS: COPPER ALLOY;
min. 200µm TIN over 80µm NICKEL
PCB-HOLE: $\phi 3,1 \pm 0,1$ mm; PCB-THICKNESS: 1,6mm
- COLLARS: COPPER ALLOY; min. 200µm over 80µm NICKEL
- P.C.B. HOLE DRILLINGS ON SHEET 2
- CONNECTOR IS PART MARKED: 16-00213□ CONEC ABC

Directive 2002/95/EC RoHS compliant


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				date	name	
				drawn	29.09.14	Henneboel
				appd.	29.09.14	Strakerjahn
				norm		
				d-old		
						
a	Original					
rev.	description	date	name			

scale: 2:1 (5:1)	
material: SEE NOTES	
title: D-SUB MALE 50pos. SOLDER PIN STRAIGHT with snap-lock and spacer clip	
dwg no:	DIN-A3
16K1A3538	sh: 1/2
part no: 16-00213□	(see note 3)

P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 3:1				
							material: SEE SHEET 1				
								date	name	title: P.C.B. HOLE DRILLINGS D-SUB MALE 50pos. SOLDER PIN STRAIGHT with snap-lock and spacer clip	
								drawn	29.09.14		
				appd.	29.09.14	Strakerjahn					
				norm		dwg no:		DIN-A3 sh: 2/2			
				d-old							
						16K1A3538					
a	Original										
rev.	description	date	name			part no: SEE SHEET 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[16-002131](#) [16-002133](#)