








P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)




SEE NOTE 4



NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. CONNECTOR IS PART MARKED: 163A16749X CONEC ABC



Directive 2002/95/EC RoHS compliant




THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm	scale:	
				date	name		material:	SEE NOTES
4 x b	Ä4102	14.09.2011	K.H.	drawn	10.04.2002	Parei	title: D-SUB HD MALE 15pos. SOLDER PIN STRAIGHT	
a	Original			appd.	10.04.2002	Mickenbecker		
rev.	description	date	name	norm				
				d-old			dwg no:	
							16K1A542	
							part no:	
							163A16749X	

CONEC

DIN-A3
sh: 1/6








1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. CONNECTOR IS PART MARKED: [163A16759X CONEC ABC]

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1 (5:1)		material: SEE NOTES	
					date			name		title: D-SUB HD MALE 26pos. SOLDER PIN STRAIGHT	
					drawn	10.04.2002	Parei				
					appd.	10.04.2002	Mickenbecker				
					norm						
					d-old						
	4 x b	Ä4102	14.09.2011	K.H.			dwg no:		DIN-A3		
	a	Original					16K1A542		sh: 2/6		
	rev.	description	date	name			part no:		163A16759X		

Directive 2002/95/EC RoHS compliant

(5:1)



NOTES:






1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. P.C.B. HOLE DRILLINGS ON SHEET 4
5. CONNECTOR IS PART MARKED: 163A16769X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale:	2:1 (5:1)							
							material:		SEE NOTES						
				DO NOT ALTER CAD DRAWING BY HAND				date		name		title: D-SUB HD MALE 44pos. SOLDER PIN STRAIGHT			
								drawn		10.04.2002				Parei	
								appd.		10.04.2002				Mickenbecker	
norm															
				d-old				dwg no: 16K1A542		DIN-A3 sh: 3/6					
4 x b		Ä4102		14.09.2011		K.H.									
a		Original													
rev.		description		date		name				part no:		163A16769X			

[illegible]

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND			tolerance		 dim. in mm		scale: 2:1 material: SEE SHEET3	
					date	name		title: P.C.B. HOLE DRILLINGS D-SUB HD MALE 44pos.	
					drawn	10.04.2002	Parei		
					appd.	10.04.2002	Mickenbecker		
					norm				
					d-old			dwg no: 16K1A542 DIN-A3 sh: 4/6	
	a	Original							
	rev.	description	date	name				part no: SEE SHEET3	



NOTES:

- METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- P.C.B. HOLE DRILLINGS ON SHEET 6
- CONNECTOR IS PART MARKED: 163A16779X CONEC ABC


Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)		
								material: SEE NOTES		
					date	name		title: D-SUB HD MALE 62pos. SOLDER PIN STRAIGHT		
					drawn	10.04.2002	Parei			
					appd.	10.04.2002	Mickenbecker			
					norm					
					d-old			dwg no: 16K1A542		
	4 x b	Ä4102	14.09.2011	K.H.			DIN-A3 sh: 5/6			
	a	Original								
	rev.	description	date	name			part no:		163A16779X	

CONEC

DIN-A3
sh: 5/6

P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 2:1					
							material: SEE SHEET 5					
								drawn	10.04.2002	Parei	title: P.C.B. HOLE DRILLINGS D-SUB HD Male 62pos.	
								appd.	10.04.2002	Mickenbecker		
								norm				
				d-old			dwg no: 16K1A542					
a	Original								DIN-A3			
rev.	description	date	name				part no: SEE SHEET 5		sh: 6/6			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A16769X](#)