





Rändel DIN 82-RAA 0.5
Knurl DIN 82.RAA 0.5



NOTES:

1. Part is splint and burr free.
2. Excellent adhesion of plating to the base material.
3. Go - no go - gauge: 4-40 UNC - 2A
M3 - g6

Bemerkungen:

1. Teil ist span- und gratfrei.
2. Gute Haftung der Oberflächen-Veredelung zum Basismaterial.
3. Prüflöhre: 4-40 UNC - 2A
M3 - g6

A	Part-No.
4-40 UNC 2A	740-360270
M3	740-368670

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish: 2µm Ni / gloss				tolerance ISO 2768-m		dim. in mm		scale:	5:1	
1 x c	Ä7432	12.09.2018	LUN	drawn	06.07.1999	name	Barcinski	material:	(b)	(c)
2 x b	Ä3747	14.09.2010	K.H.	appd.	06.07.1999	Mickenbecker		title:	JACK SCREW for Hood 9-50pol. D-SUB for Hood	
a	Original			norm				dwg no:	(b)	DIN-A4
rev.	description	date	name	d-old				part no:	SEE TABLE	

CONEC®

scale:		5:1	
material:		(b) AISI-12L14 Steel 1.0737 oder Steel 1.0718 (c)	
title:		JACK SCREW for Hood 9-50pol. D-SUB for Hood	
dwg no:		(b)	DIN-A4
740FER0A		sh: 1	
part no:		SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[740-360270](#) [740-368670](#)