






STRIPPING
DIMENSION (b)



Part-no. as per finish			
(b) GOLD FLASH over NICKEL (c)	min. 20µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	min. 50µin HARD GOLD over min. 50µin NICKEL
162A18709X	162B18709X	162C18709X	162J18709X

- (b) **NOTES:**
1. Material: Copper alloy
 2. Finish: See table
 3. Temperature range: -55 °C to +125 °C
 4. Rated current: 7.5 A maximum
 5. Contact resistance: ≤ 10 mOhm
 6. Crimping: Use crimp tool 360X10329X
With tool insert 360X20069X
Selector settings: 7 for AWG 20
6 for AWG 22
5 for AWG 24

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND				tolerance DIN ISO 2768-m		dim. in mm
3 x d	Ä5346	17.09.2014	K.H.	norm		
1 x c	Ä 4116	26.09.11	Lehm.	d-old		
4 x b	Ä 3698	25.08.10	Lehm.			
a	Original					
rev.	description	date	name			

CONEC®

scale:	5:1	
material:	SEE NOTES	
title:	CRIMP SOCKET CONTACT screw machined version accepts cable AWG 24-20	
dwg no:	Inventor 10	DIN-A4
	16K1A929	sh: 1
part no:	SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[162A18709X](#)