







NOTES: (b)

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY; PLATING (SEE PART NO.):
☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
- THREADED SPACER CLIPS:
 COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
 PCB-HOLE: $\varnothing 3.1 \pm 0,1$; PCB THICKNESS 1,6mm
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 163□16239X CONEC ABC (see note 3)

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH


DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
					date	name	
				drawn	02.09.2014	Heinrich	
				appd.		Lehmenkühler	
				norm			
				d-old	16K1A914		
5 x b	Ä5325	02.09.2014	Heinrich				
a	Original						
rev.	description	date	name				

CONEC

part no: (b) 163□16239X (see note 3)		DIN-A3	
		sh: 1/2	

P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance		 dim. in mm	scale: 3:1	
								material: see sheet 1	
					date	name	title: P.C.B. HOLE DRILLINGS D-SUB MALE 37pos. SOLDER PIN STRAIGHT with threaded spacer clip		
					drawn 02.09.2014	Heinrich			
					appd.	Lehmenkühler			
					norm				
					d-old		dwg no:		DIN-A3 sh: 2/2
							16K1A3510		
	a	Original							
rev.	description	date	name						
						part no:		SEE SHEET 1	

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A16239X](#)