


Specification of Quartz Crystal Units

1 NDK Part Number	NX3215SA-32.768kHz-EXS00A-MU00003
2 Chipset Maker	STMicroelectronics
3 Application	BLE
4 Chipset Name	BlueNRG
5 NDK Specification Number	EXS00A-MU00003
6 Type	NX3215SA
7 Electrical Characteristics	

	Parameters	SYM.	Electrical Spec.				Notes
			min	typ	max	Units	
1	Nominal Frequency (f _{nom})	f _{nom}	32.768			kHz	
2	Overtone order	-	Fundamental			-	
3	Frequency tolerance	-	-20	-	+20	ppm	at +25°C
4	Turning Point	-	+25+/-5			°C	
5	Temperature coefficient	-	-0.04 Max.			ppm/°C ²	
6	Equivalent Series Resistance	R _r	-	-	90	kΩ	Network Analyzer(CNA-LF made in Transat corp.)
7	Load capacitance	CL	-	12.5	-	pF	Network Analyzer(CNA-LF made in Transat corp.)
8	Level of drive	-	-	0.1	0.5	μW	
9	Insulation resistance	-	500	-	-	Ω	*1.
10	Operating temperature range	Topr	-40	-	+85	°C	
11	Storage temperature range	Tstr	-40	-	+85	°C	

*1. Terminal to terminal insulation resistance must be 500MΩ (Min.) when DC100V ±15V is applied.

Dimension



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NDK:](#)

[NX3215SA-32.768K-EXS00A-MU00003](#) [MU00003-32.768K](#)