






STRIPPING
DIMENSION (b) (d)



(d)

Part-no. as per finish		
GOLD FLASH over NICKEL (e)	min. 20µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL
162A18419X	162B18419X	162C18419X

(b) (c) (d) NOTES:

1. Material: Copper alloy
2. Finish: See table
3. Temperature range: -55 °C to +125 °C
4. Rated current: 3 A maximum
5. Contact resistance: ≤ 10 mOhm
6. Crimping: Use crimp tool 360X10329X
With tool insert 360X10629X
Selector settings: 4 for AWG 22
3 for AWG 24
2 for AWG 26
1 for AWG 28

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance DIN ISO 2768-m		dim. in mm
				date	name	
1 x e	Ä 4116	26.09.11	Lehm.	appd.	12.03.01	Mickenbecker
4 x d	Ä 3698	25.08.10	Lehm.	norm		
1 x c	Ä 3679	24.06.10	Petker	d-old		
2 x b	Ä 2647	11.01.07	Lehm.			
a	Original					
rev.	description	date	name			

CONEC®

scale:	5:1	
material:	SEE NOTES	
title:	HD CRIMP SOCKET CONTACT screw machined version accepts cable AWG 28-22	
dwg no:	Inventor 10	DIN-A4
	16K1A153A	sh: 1
part no:	SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[162A18419X](#) [162C18419X](#)