


1	NDK Part Number	NX3225GA-32M-EXS00A-CG02611
2	Chipset Maker	Texas Instruments
3	Application	Second Generation System-on-Chip Solution for 2.4 GHz IEEE 802.15.4 / RF4CE / ZigBee
4	Chipset Name	CC253X (0,1,3) CC2540
5	NDK Specification Number	EXS00A-CG02611
6	Type	NX3225GA
7	Electrical Characteristics	
7.1	Nominal Frequency (f_{nom})	32.000 MHz
7.2	Overtone order	Fundamental
7.3	Frequency tolerance	$\pm 20 \times 10^{-6}$ max.
7.4	Frequency versus temperature characteristics	$\pm 20 \times 10^{-6}$ max. (at +/-0 to +70 °C)
7.5	Equivalent Series Resistance (R_r)	50 Ω max.
7.6	Maximum Drive Level	200 μ W max.
7.7	Aging (at +25 °C)	---
8	Measurement Circuit	
8.1	Frequency Measurement	
8.1.1	Measuring Instrument	IEC π -Network
8.1.2	Load Capacitance (C_L)	10pF
8.1.3	Level of Drive	10 μ W
8.2	Equivalent Resistance Measurement	
8.2.1	Measuring Instrument	IEC π -Network
8.2.2	Load Capacitance (C_L)	Series
8.2.3	Level of Drive	10 μ W
9	Operating Temperature Range	0 to +70 °C
10	Storage Temperature Range	-40 to +85 °C
11	Dimension	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NDK:

[NX3225GA-32M-EXS00A-CG02611](#)