



Inventek Systems

Wi-Fi Dual Band Antennas 2.4 & 5 GHz

P/N: W245-SC




Table of Contents

1	General Description	3
2	Part Number Detail Description.....	3
2.1	Ordering Information	3
3	General Features	3
4	Applications	3
5	Electrical Specifications.....	4
5.1	2400-2500 MHz Band.....	4
5.2	4900-5900 MHz Band.....	4
5.3	Return Loss (S_{11}).....	5
5.4	VSWR (S_{11})	5
5.5	Smith Chart (S_{11}).....	6
6	Antenna Dimensions (unit: mm).....	6
7	Radiation Pattern.....	7
7.1	2400-2500 MHz Band.....	7
7.1.1	3D Gain Pattern at 2442 MHz	7
7.1.2	Efficiency Table.....	8
7.1.3	Efficiency vs. Frequency	8
7.2	4900-5900 MHz Band.....	9
7.2.1	3D Gain Pattern at 5150 MHz	9
7.2.2	3D Gain Pattern at 5550 MHz	10
7.2.3	3D Gain Pattern at 5850 MHz	11
7.2.4	Efficiency Table.....	12
7.2.5	Efficiency vs. Frequency	12
8	RoHS.....	13
9	Revision Control	13
10	Contact Information	13

1 General Description

The [Inventek](#) 2400-2500 and 4900-5900 MHz Dual Band Wi-Fi Chip antennas let you integrate Wi-Fi functionality into your product quickly and easily. It's suitable for a wide range of applications and recommended for use with Inventek ISM4334x module family.

2 Part Number Detail Description

2.1 Ordering Information

Device	Description	Ordering Number
W245-SC	2400-2500 & 4900-5900 MHz Dual Band Wi-Fi chip antenna	W245-SC

3 General Features

- Stable and reliable in performances
- Reference layout guideline for Inventek modules available
- Compact size
- RoHS compliance
- SMT Process compatible

4 Applications

- IEEE802.11 (a/b/g/n/ac).
- Hand-held devices when WiFi (802.11 a/b/g/n/ac) functions are needed.

5 Electrical Specifications

5.1 2400-2500 MHz Band


Characteristics		Specifications	Unit
Outline Dimensions		3.2 x 1.6 x 0.5	mm
Working Frequency		2400~2500	MHz
Bandwidth		90 (typical)	MHz
VSWR		2 max.	
Impedance		50	Ω
Polarization		Linear Polarization	
Gain	Peak	1.4 (typical)	dBi
	Efficiency*	79 (typical)	%

5.2 4900-5900 MHz Band


Characteristics		Specifications	Unit
Working Frequency		5150~5850	MHz
Bandwidth		700 (typical)	MHz
VSWR		2 max.	
Impedance		50	Ω
Polarization		Linear Polarization	
Gain	Peak	2.3 (typical)	dBi
	Efficiency*	71 (typical)	%

*Efficiency may vary depending on size of the user's ground plane


5.3 Return Loss (S_{11})




5.4 VSWR (S_{11})



5.5 Smith Chart (S_{11})



6 Antenna Dimensions (unit: mm)







7 Radiation Pattern

All Radiation patterns were measured with the antenna on a 80 x 40 mm ground plane

7.1 2400-2500 MHz Band


7.1.1 3D Gain Pattern at 2442 MHz



7.1.2 Efficiency Table





Frequency(GHz)	2.400	2.412	2.417	2.422	2.427	2.432	2.437	2.442	2.447	2.452	2.457	2.462	2.467	2.472	2.484
Efficiency(dB)	-1.68	-1.35	-1.18	-1.04	-0.98	-1.04	-1.11	-1.14	-1.15	-1.12	-1.07	-1.01	-1.01	-1.07	-1.46
Efficiency(%)	67.94	73.21	76.13	78.67	79.87	78.75	77.37	76.83	76.75	77.20	78.09	79.28	79.18	78.13	71.45
Gain(dBi)	0.75	1.17	1.32	1.38	1.40	1.30	1.32	1.40	1.48	1.45	1.44	1.46	1.39	1.32	1.17

7.1.3 Efficiency vs. Frequency







7.2 4900-5900 MHz Band





7.2.1 3D Gain Pattern at 5150 MHz



7.2.2 3D Gain Pattern at 5550 MHz




7.2.3 3D Gain Pattern at 5850 MHz



7.2.4 Efficiency Table

Frequency(GHz)	5.150	5.200	5.250	5.300	5.350	5.400	5.450	5.500	5.550	5.600	5.650	5.700	5.750	5.800	5.850
Efficiency(dB)	-1.46	-1.43	-1.83	-1.45	-1.43	-1.82	-1.99	-1.55	-1.72	-1.58	-1.44	-1.62	-1.77	-1.54	-1.90
Efficiency(%)	71.45	71.88	65.67	71.64	71.90	65.78	63.19	69.92	67.32	69.56	71.73	68.92	66.58	70.09	64.56
Gain(dBi)	2.15	2.30	2.00	2.28	2.14	2.06	1.98	2.39	2.34	2.75	2.88	2.56	2.48	2.55	2.16

7.2.5 Efficiency vs. Frequency



8 RoHS

Restriction of Hazardous Substances (RoHS) directive has come into force since 1st July 2006 all electronic products sold in the EU must be free of hazardous materials, such as lead.

9 Revision Control

Document : W245-SC	2.4_5GHz Dual Band Wi-Fi antenna
Internal Release	DOC-DS-20105

Date	Author	Revision	Comment
5/10/2016	KMT	1.0	Preliminary

10 Contact Information

Inventek Systems
2 Republic Road
Billerica Ma, 01862
Tel: 978-667-1962
Sales@inventeksys.com

www.inventeksys.com

Inventek Systems reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. The information contained within is believed to be accurate and reliable. However Inventek Systems does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inventek Systems:](#)

[W245-SC](#)