







4				3				2				1																																																																																																									
												used for: D-SUB																																																																																																									
<table><tr><th>Wire size AWG</th><th>Crimp height A</th></tr><tr><td>24</td><td>0,68 - 0,86</td></tr><tr><td>22</td><td>0,68 - 0,86</td></tr><tr><td>20</td><td>0,68 - 0,86</td></tr></table> 												Wire size AWG	Crimp height A	24	0,68 - 0,86	22	0,68 - 0,86	20	0,68 - 0,86																																																																																																		
Wire size AWG	Crimp height A																																																																																																																				
24	0,68 - 0,86																																																																																																																				
22	0,68 - 0,86																																																																																																																				
20	0,68 - 0,86																																																																																																																				
STRIPPING DIMENSIONS 																																																																																																																					
Directive 2002/95/EC RoHS compliant NOTES: Material: Phosphor Bronze ⓑ Finish: Gold Flash over Nickel in the Contact Area Temperature Range: -55°C to +125°C Rated Current: 7.5A Contact Resistance: <= 10mOhm Crimping: Use Crimp Tool 360X10079X																																																																																																																					
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND <table><tr><td colspan="4">finish:</td><td colspan="4">tolerance</td><td colspan="2"> dim. in mm</td><td colspan="4">scale: 5:1</td></tr><tr><td colspan="4">SEE NOTES</td><td colspan="4"></td><td colspan="2"></td><td colspan="4">material: SEE NOTES</td></tr><tr><td></td><td></td><td></td><td></td><td>2008</td><td>date</td><td colspan="2">name</td><td colspan="6" rowspan="5">title: PLUG CONTACT CRIMP AWG 24-20 (big spool wheeled left)</td></tr><tr><td></td><td></td><td></td><td></td><td>drawn</td><td>25.01.</td><td colspan="2">Schmidt</td></tr><tr><td></td><td></td><td></td><td></td><td>appd.</td><td>25.01.</td><td colspan="2">Mickenbecker</td></tr><tr><td></td><td></td><td></td><td></td><td>norm</td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>d-old</td><td colspan="2"></td></tr><tr><td>1 x b</td><td>Ä 4116</td><td>26.09.2011</td><td>Lehmen.</td><td colspan="4" rowspan="3"></td><td colspan="2">dwg no:</td><td colspan="2">AutoCAD 2006</td><td colspan="2">DIN-A</td></tr><tr><td>a</td><td>Original</td><td></td><td></td><td colspan="2">16K2A618</td><td colspan="2">4</td></tr><tr><td>rev.</td><td>description</td><td>date</td><td>name</td><td colspan="2">part no: 161A13369X</td><td colspan="2">sh: 1/1</td></tr></table>												finish:				tolerance				 dim. in mm		scale: 5:1				SEE NOTES										material: SEE NOTES								2008	date	name		title: PLUG CONTACT CRIMP AWG 24-20 (big spool wheeled left)										drawn	25.01.	Schmidt						appd.	25.01.	Mickenbecker						norm							d-old			1 x b	Ä 4116	26.09.2011	Lehmen.					dwg no:		AutoCAD 2006		DIN-A		a	Original			16K2A618		4		rev.	description	date	name	part no: 161A13369X		sh: 1/1					
finish:				tolerance				 dim. in mm		scale: 5:1																																																																																																											
SEE NOTES										material: SEE NOTES																																																																																																											
				2008	date	name		title: PLUG CONTACT CRIMP AWG 24-20 (big spool wheeled left)																																																																																																													
				drawn	25.01.	Schmidt																																																																																																															
				appd.	25.01.	Mickenbecker																																																																																																															
				norm																																																																																																																	
				d-old																																																																																																																	
1 x b	Ä 4116	26.09.2011	Lehmen.					dwg no:		AutoCAD 2006		DIN-A																																																																																																									
a	Original							16K2A618		4																																																																																																											
rev.	description	date	name					part no: 161A13369X		sh: 1/1																																																																																																											
4				3				2				1																																																																																																									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[161A13369X](#)