

## Notes

## SPECIFICATIONS

## Materials

Insulator: High Temperature Thermoplastic UL94V-0.

Contact: Phosphor Bronze

30u" Gold Plated over Nickel on mating area

Tin Plated over Nickel on Solder tail

Metal Board Lock: Zinc Alloy, 150u" Tin Plated

Shell: Zinc Alloy, 150u" Nickel Plated

## Electrical

Insulation Resistance: 2000 Megohms Min.


Contact Resistance: 20mΩ MAX. (Initial)

Current Rating: 1.5 AMP.



Voltage Rating: 250 VAC R.M.S.

Dielectric Withstanding Voltage: 500 VAC (R.M.S.)



Temperature Range:  $-55^{\circ}\text{C} \sim 85^{\circ}\text{C}$



TYPE:1



Directive 2002/95/EC  
„RoHS“  
Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT © CONEC CORPORATION	<b>tolerance</b> unless otherwise specified tolerance shall be as follow Decimal: $\frac{x}{100}$ Angles: $\frac{x}{1000}$				<b>finish</b>		 Dim. in mm	<b>scale:</b>		
								<b>material:</b> SEE NOTES		
	<b>title:</b> DVI 29p female R/A connector with 4-40 UNC thread (RoHS)									
					2006	date	name	<b>drawing no.:</b> AutoCAD 2005		
					draw.	April 06	Vincent Ke			
					appd.	April 06	Kathy Skelthorn			
					norm					
				d-old			<b>DIN</b> A3			
a	origin									
rev.	description	date	name				<b>part no.:</b> 33DVR-29S12R			
								sheet 1/1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[33DVIR-29S12R](#)