



**FEATURES**

- ※3-state setting
- ※Low profile for space saving


**APPLICATION**

- ※Remote control
- ※Home automation
- ※Telecommunication

**SPECIFICATION**

Contact Rating	25mA, 24V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	500V AC/1 minute
Operating Force	1,000gf max.
Travel	0.8mm
Operating Life	2,000 cycles
Operating Temp.	-20°C ~ +85°C
Storage Temp.	-40°C ~ +85°C

**HOW TO ORDER**



**CIRCUIT**



**PACKAGE**

- <Tube>  
 TII(R)/TIM(R)-04: 41 pcs  
 TII(R)/TIM(R)-05: 34 pcs  
 TII(R)/TIM(R)-08: 22 pcs  
 TII(R)/TIM(R)-09: 20 pcs  
 TII(R)/TIM(R)-10: 18 pcs
- <Tape & Reel>  
 TIM(R): 900 pcs

**TII(R)**





PART NO.	NO. OF POS.	DIM.A	DIM.B
TII(R)-04	4	11.32	7.62
TII(R)-05	5	13.86	10.16
TII(R)-08	8	21.48	17.78
TII(R)-09	9	24.02	20.32
TII(R)-10	10	26.56	22.86




P.C.B. LAYOUT

TIM(R)

DIP SWITCH



PART NO.	NO.OF POS.	DIM.A	DIM.B
TIM(R)-04	4	11.32	7.62
TIM(R)-05	5	13.86	10.16
TIM(R)-08	8	21.48	17.78
TIM(R)-09	9	24.02	20.32
TIM(R)-10	10	26.56	22.86



P.C.B. LAYOUT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Diptronics:

[TIM-05-V-T/R](#) [TIMR-09-T-V-T/R](#) [TIM-10-V-T/R](#) [TII-05-V](#) [TIMR-10-T-V-T/R](#) [TII-04-V](#) [TIMR-05-T-V-T/R](#) [TIM-09-V-T/R](#) [TII-10-V](#) [TIMR-08-T-V-T/R](#) [TIM-08-V-T/R](#) [TIMR-04-T-V-T/R](#) [TIM-04-V-T/R](#) [TII-08-V](#) [TII-09-V](#)