




FEATURES

- ※ Variety of actuator lengths
- ※ Optional ground pin
- ※ Cap options


APPLICATION

- ※ Audio, OA equipment
- ※ Instrumentation
- ※ Setup box


SPECIFICATION

Contact Rating	50mA, 12V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	250V AC/1 minute
Operating Force	100±50gf, Black(K) 160±50gf, Brown(N) 260±50gf, Red(R) 320±80gf, Salmon(S) 520±130gf, Yellow(Y)
Travel	0.25mm
Operating Life	Phosphor Bronze Dome 50,000 cycles for 520/320gf 100,000 cycles for 260gf 200,000 cycles for 160/100gf Stainless Steel Dome 300,000 cycles for 520/320gf 500,000 cycles for 260gf 1,000,000 cycles for 160/100gf
Operating Temp.	-25°C ~ +70°C
Storage Temp.	-30°C ~ +80°C

HOW TO ORDER




CIRCUIT





PACKAGE

<Bag>
DTSA(G)-6: 500 pcs
<Tape & Reel>
DTSAM-6: 500 pcs
DTSAMG-61, 62: 500 pcs
DTSAMG-63, 64, 65: 380 pcs


DTSA-6





PART NO.	H
DTSA-61	3.15
DTSA-62	3.85
DTSA-63	5.85
DTSA-644	6.15(SQ.2.40)
DTSA-648	6.15(SQ.2.80)
DTSA-65	8.35
DTSA-66	11.85



DTSAG-6




PART NO.	H
DTSAG-61	4.30
DTSAG-62	5.00
DTSAG-63	7.00
DTSAG-644	7.30(SQ.2.40)
DTSAG-648	7.30(SQ.2.80)
DTSAG-65	9.50
DTSAG-66	13.00





P.C.B. LAYOUT

TACT SWITCH

DTSAMG-6




PART NO.	H
DTSAMG-61	4.30
DTSAMG-62	5.00
DTSAMG-63	7.00
DTSAMG-644	7.30(SQ.2.40)
DTSAMG-648	7.30(SQ.2.80)
DTSAMG-65	9.50
DTSAMG-66	13.00






P.C.B. LAYOUT

DTSAM-6



PART NO.	H
DTSAM-61	3.60
DTSAM-62	4.30
DTSAM-63	6.30
DTSAM-644	7.30(SQ.2.40)
DTSAM-648	7.30(SQ.2.80)
DTSAM-65	8.80



P.C.B. LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diptronics:](#)

[DTSAM-61N/K-S-Q-T/R](#) [DTSAMG-63N-Q-T/R](#) [DTSAMG-62N-Q-T/R](#) [DTSAMG-63R-Q-T/R](#) [DTSAMG-66K-Q-T/R](#)
[DTSAMG-65R-Q-T/R](#) [DTSAM-63N-S-Q-T/R](#) [DTSAMG-61N-Q-T/R](#) [DTSAMG-65K-Q-T/R](#) [DTSAM-62N-S-Q-T/R](#)
[DTSAMG-66R-Q-T/R](#) [DTSAMG-62K-Q-T/R](#) [DTSAMG-644N-Q-T/R](#) [DTSAM-63R-S-Q-T/R](#) [DTSAM-644N-S-Q-T/R](#)
[DTSAM-65R-S-Q-T/R](#) [DTSAMG-65N-Q-T/R](#) [DTSAM-62R-S-Q-T/R](#) [DTSAM-644R-S-Q-T/R](#) [DTSAMG-66N-Q-T/R](#)
[DTSAM-61R-S-Q-T/R](#) [DTSAMG-63K-Q-T/R](#) [DTSAM-61N-S-Q-T/R](#) [DTSAMG-62R-Q-T/R](#) [DTSAMG-644K-Q-T/R](#)
[DTSAM-65N-S-Q-T/R](#) [DTSAMG-644R-Q-T/R](#) [DTSAMG-61K-Q-T/R](#) [DTSAMG-61R-Q-T/R](#)