






D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	8pos 30 V
Current rating: IEC 61076-2-101	2 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperatur range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PBT, UL 94
Coupling screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1	white	5	grey
2	brown	6	pink
3	green	7	blue
4	yellow	8	red
Shielding coupling screw			

Part no:	Description:	Length L:	Cable:
43-10980	SAL - 12S - RS8 - 2 / G3	2m	PVC, UL 2464, grey, 8x0,25mm ² Cable: 781-G32800
43-10981	SAL - 12S - RS8 - 3 / G3	3m	
43-10982	SAL - 12S - RS8 - 5 / G3	5m	
43-10983	SAL - 12S - RS8 - 10 / G3	10m	
43-xxxxx	SAL - 12S - RS8 - ... / G3	x	

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: b 12.12.10 VF Ä3767 Coupling screw modified, spanner flats added, data sheet modified
		tolerance of cable: $L \leq 4\text{m}: L + 40\text{mm}$ $L > 4\text{m}: L + 1\%$
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

dim. in mm		
	date	name
drawn	14.03.07	Mankopf
appd.	14.03.07	Fromm

title:		Male connector M12x1 axial, 360°-shielding
dwg no:		43K1A428
part no:		see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10982](#) [43-10980](#) [43-10983](#) [43-10981](#)