


Technical specification:

Rated voltage: IEC 61076-2-101	3pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1)	brown
3)	blue
4)	black

D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-10180	SAL - 12 - RKW3 - 2 / K1	2m	TPU, UL 20549, black, 3x0,34mm ² Cable: 781-K13300
43-10181	SAL - 12 - RKW3 - 3 / K1	3m	
43-10182	SAL - 12 - RKW3 - 5 / K1	5m	
43-10183	SAL - 12 - RKW3 - 10 / K1	10m	
43-xxxxx	SAL - 12 - RKW3 - ... / K1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 11.10.10 VF A3767 Coupling nut modified, spanner flats added, data sheet modified		 dim. in mm		title: Female connector M12x1 angled	
				date		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn	08.03.07	Burschik	dwg no: 43K1A362
			appd.	08.03.07	Mankopf	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10182](#) [43-10181](#) [43-10180](#) [43-10183](#)