


D see data sheet cable

Technical specification :

Rated voltage: 3pos
IEC 61076-2-101 250 V

Current rating: 4 A at 40°C
IEC 61076-2-101

Insulation resistance: >=100 MΩ
IEC 60512

Pollution degree: 3/2
IEC 60664-1

Degree of protection: IP 67, in mated condition
IEC 60529

Temperature range: -30°C ... +80°C
IEC 60664-1

Mating cycles: >=100
IEC 60512-9a

Materials:

Contact: CuZn

Contact plating: Nickel, gold plated

Contact carrier: TPU GF, UL 94

Sealing: FPM

Coupling nut: GD-Zn, nickel plated

Moulding body: TPU, UL 94, grey

Installation specification:


Recommended torque: 0,6 Nm

Conec installation tool: Torque wrench: 36-000200
Insert across flats 13: 36-000220

Contact assignment:

- 1) brown
- 3) blue
- 4) black

Part no:	Description:	Length L:	Cable:
43-10012	SAL - 12 - RK3 - 2 / K1	2m	TPU, UL 20549, black, 3x0,34mm ² Cable: 781-K13300
43-10013	SAL - 12 - RK3 - 3 / K1	3m	
43-10014	SAL - 12 - RK3 - 5 / K1	5m	
43-10015	SAL - 12 - RK3 - 10 / K1	10m	
43-xxxxx	SAL - 12 - RK3 - ... / K1	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 11.01.11 VF Ä3767 Coupling nut modified, spanner flats added, data sheet modified	 dim. in mm	title: Female connector M12x1 axial	
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		dwg no: 43K1A379	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm		part no: see table	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10015](#) [43-10013](#) [43-10012](#) [43-10014](#)