





Technical specification:

Rated voltage: IEC 61076-2-101	4pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey
Installation specification:	
Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220




Contact assignment:

- 1) brown
- 2) white
- 3) blue
- 4) black



D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-14609	SAL - 12 - RK4 - RSW4 - 0,3 / K1 / A1090	0,3m	TPU, UL 20549, black, 4x0,34mm² Cable: 781-K13400
43-14610	SAL - 12 - RK4 - RSW4 - 0,6 / K1 / A1090	0,6m	
43-14611	SAL - 12 - RK4 - RSW4 - 1,5 / K1 / A1090	1,5m	
43-14612	SAL - 12 - RK4 - RSW4 - 3,0 / K1 / A1090	3m	
43-xxxxx	SAL - 12 - RK4 - RSW4 - ... / K1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	 dim. in mm		title: Connecting cable M12x1, female connector axial - male connector angled
	date	name	
	drawn 17.01.11	Franz	dwg no: 43K1A1278
	appd. 17.01.11	Mankopf	
tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%			part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			
			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14612](#) [43-14611](#) [43-14609](#) [43-14610](#)