


D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	4pos 160 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	≥ 100 M Ω
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperatur range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn, CuBe
Contact plating:	Nickel, gold plated
Contact carrier:	PA, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1	n.c.
2	Profibus-A green
3	n.c.
4	Profibus-B red
	Shielding coupling nut

Part no:	Description:	Length L:	Cable:
43-12479	SAL - 12B - RKW4.1 - 2 / G7	2m	TPE, UL, violet, 2xAWG24 Cable: 781-G70200
43-12480	SAL - 12B - RKW4.1 - 3 / G7	3m	
43-12481	SAL - 12B - RKW4.1 - 5 / G7	5m	
43-12482	SAL - 12B - RKW4.1 - 10 / G7	10m	
43-xxxxx	SAL - 12B - RKW4.1 - ... / G7	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 09.03.2011 VF Ä3767 Coupling nut modified, spanner flats added, data sheet modified
	tolerance of cable: L $\leq$ 4m: L + 40mm L > 4m: L + 1%
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH



dim. in mm

	date	name
drawn	17.10.08	Mankopf
appd.	17.10.08	Fromm



title:	Female connector M12x1 angled, Profibus DP
dwg no:	43K1A786
part no:	see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-12482](#) [43-12479](#) [43-12480](#) [43-12481](#)