

d

Technical specification:



Technische Daten:

Working voltage/ Betriebsspannung:	125 V
Initial contact resistance/ Anfangs- Durchgangswiderstand:	≤ 15 mΩ
Temperature range/ Temperaturbereich:	- 55 °C ... + 125 °C
Mating cycles/ Steckzyklen:	Quality class 1 = 500 Gütestufe 1 Quality class 2 = 400 Gütestufe 2 Quality class 3 = 50 Gütestufe 3

Materials/

Werkstoffe:

Contact/ Kontakt:	Cu alloy, Au over Ni
Insulator/ Isolierkörper:	PBT GF UL 94 V-0, grey/grau







48 Holes for code pins Ø1 x 4,5mm deep/
48 Bohrungen für Kodierstifte Ø1 x 4,5mm tief

d

Part no. / Part marked / Art.-Nr. / Bedruckung:	Contact plating / Kontakt Veredelung:
122A11059X	Gold over nickel / 50 mating cycles Gold über Nickel / 50 Steckzyklen
122B11059X	Gold over nickel / 400 mating cycles Gold über Nickel / 400 Steckzyklen
122C11059X	Gold over nickel / 500 mating cycles Gold über Nickel / 500 Steckzyklen

				dim. in mm		Female Connector Type "F" 48pos. solder pin straight/ 1x1mm <i>Federleiste Type "F"</i> 48pol. Lötstift gerade / 1x1mm	
			Date/ datum	Name			
		drawn/ gez.	19.05.1999	Barcinski			
		appd./ gepr.	18.05.1999	Mickenbecker			
Index: d Ä7479 25.09.18 KHE	scale/stab: 2:1			dwg no / Z.-nr.:		12K1IH4A	DIN- A3
Status: InBearbeitung							1 / 2
RoHS compliant/ konform							

PCB hole drillings (PCB top side)/
Leiterplattenbohrbild (Leiterplatten Oberseite)



		dim. in mm		Female Connector Type "F" 48pos. solder pin straight/ 1x1mm Federleiste Type "F" 48pol. Lötstift gerade / 1x1mm	
		Date/Datum	Name		
		drawn/gez. 19.05.1999	Barcinski		
		appd./gepr. 18.05.1999	Mickenbecker		
Index: d Ä7479 25.09.18 KHE	scale/maßstab: 2:1				dwg no / Z.-nr.: 12K1IH4A
Status: InBearbeitung					DIN-A3
RoHS compliant/ konform					2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[122A11059X](#)