


Technical specification :

Rated voltage: IEC 61076-2-104	60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: EN 60512-11-10 EN 60512-11-4	-20°C ... +80°C -40°C -40°C ... +85°C
Mating cycles: IEC 60512-9a	>=100

Cable specification:

Temperatur range:	
static	-20°C ... +80°C
flexibel	-5°C ... +80°C

Materials:

Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	PA, UL 94 V-0
	FPM
Sealing:	
Coupling nut /screw:	GD-Zn, Nickel plated
Moulding body:	TPU, UL 94 HB, grey


Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1	brown	
3	blue	
4	black	
	Shielding	
	coupling nut/	
	screw	

Part no:	Description:	Length L:	Cable:
42-10875	SAL - 8S - RK3 - RS3 - 0,3 / G3	0,3m	PVC, UL 2464, grey, 3x0,25mm² Cable: 781-G32300
42-10876	SAL - 8S - RK3 - RS3 - 0,6 / G3	0,6m	
42-10877	SAL - 8S - RK3 - RS3 - 1,5 / G3	1,5m	
42-10878	SAL - 8S - RK3 - RS3 - 3 / G3	3,0m	
42-xxxxx	SAL - 8S - RK3 - RS3 - ... / G3	x	

DO NOT ALTER CAD DRAWING BY HAND RoHS & REACH compliant	Index a: Ä6110 rbo 13.06.16 Data sheet modified, moulding body modified		 dim. in mm		title: Connecting cable M8x1, 360°-shielding, female connector axial - male connector axial	
			date	name		
	tolerance of cable: L <= 4m: L + 40mm 					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-10876](#) [42-10877](#) [42-10875](#) [42-10878](#)