


Contact assignment:

1	white	1
2	brown	2
3	green	3
4	yellow	4
5	grey	5
6	pink	6
7	blue	7
8	red	8
Shielding coupling nut/-screw		

Technical specification :

Rated voltage:	30 V
IEC 61076-2-104	
Current rating:	1,5 A bei 40°C
IEC 61076-2-104	
Insulation resistance:	>=100 MΩ
IEC 60512	
Pollution degree:	3/2
IEC 60664-1	
Degree of protection:	IP 67, in mated condition
IEC 60529	
Temperature range:	-30°C ... +80°C
EN 60512-11-10	
EN 60512-11-4	-40°C ... +85°C
Mating cycles:	>=100
IEC 60512-9a	

Cable specification:


Temperatur range:	
static	-30°C ... +80°C
flexibel	-15°C ... +80°C

Materials:

Contact:	CuZn, Ni b / Au 0,2 gal.
Contact carrier:	PA, UL 94 V-0
Sealing:	FPM
Coupling nut/-screw:	GD-Zn, Nickel plated
Moulding body:	TPU, UL 94 HB, grey
Shielding bush:	CuZn, Nickel plated

Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210



Part-no:	Description:	Length L:	Cable:
42-12206	SAL - 8S - RK8 - RS8 - 0,3 / G3	0,3m	PVC, UL 2464, grey, 8x0,14mm² Cable: 781-G31800
42-12207	SAL - 8S - RK8 - RS8 - 0,6 / G3	0,6m	
42-12208	SAL - 8S - RK8 - RS8 - 1,5 / G3	1,5m	
42-12209	SAL - 8S - RK8 - RS8 - 3 / G3	3m	
42-xxxxx	SAL - 8S - RK8 - RS8 - ... / G3	x	

DO NOT ALTER CAD DRAWING BY HAND


RoHS & REACH compliant

Index a: 01.06.2015 rch Ä5648
Data sheet changed

tolerance of cable: L ≤ 4m: L + 40mm
L > 4m: L + 1%

general tolerance: 0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm
+ ± 5°

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH



dim. in mm

	date	name
drawn	25.09.13	Christen
appd.	25.09.13	Mankopf

CONEC®

title:

Connecting cable M8x1, 360°-shielding,
female connector axial - male connector
axial

dwg no:

42K1A561

part no:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-12208](#) [42-12209](#) [42-12206](#) [42-12207](#)