


D see data sheet cable

Technical specification :

Rated voltage: IEC 61076-2-104	30 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PA, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey


Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1)	brown
2)	white
3)	blue
4)	black

Part no:	Description:	Length L:	Cable:
42-10048	SAL - 8 - RKW4 - 2 / A1	2m	PVC, grey, 4x0,25mm ² Cable: 781-A12400
42-10049	SAL - 8 - RKW4 - 3 / A1	3m	
42-10050	SAL - 8 - RKW4 - 5 / A1	5m	
42-10051	SAL - 8 - RKW4 - 10 / A1	10m	
42-xxxxx	SAL - 8 - RKW4 - ... / A1	x	

DO NOT ALTER CAD DRAWING BY HAND RoHS & REACH compliant	Index c - Å5521 05.02.15 rbo Material conact carrier was TPU		 dim. in mm		title: Female connector M8x1 angled	
			date	name		
	tolerance of cable:	L <= 4m: L + 40mm L > 4m: L + 1%	drawn	04.10.07	Franz	dwg no:
			appd.	04.10.07	Mankopf	
	general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				42K1A013
part no: see table						

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

CONEC®

part no: see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-10050](#) [42-10048](#) [42-10049](#) [42-10051](#)