








Technical specification :

Rated voltage: IEC 61076-2-104	60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

1) brown	■
3) blue	■
4) black	■

Part no:	Description:	Length L:	Cable:
42-10149	SAL - 8 - RKW3 - RS3 - 0,3 / A1	0,3m	PVC, grey, 3x0,25mm ² Cable: 781-A12300
42-10150	SAL - 8 - RKW3 - RS3 - 0,6 / A1	0,6m	
42-10151	SAL - 8 - RKW3 - RS3 - 1,5 / A1	1,5m	
42-10152	SAL - 8 - RKW3 - RS3 - 3 / A1	3,0m	
42-xxxxx	SAL - 8 - RKW3 - RS3 - ... / A1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: a 17.03.11 VF Ä3945 Coupling nut/ screw modified, spanner flats added, data sheet modified	 dim. in mm			title: Connecting cable M8x1, female connector angled - male connector axial
			date	name		
		tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	13.12.07	Franz	dwg no:
			appd.	13.12.07	Mankopf	
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-10151](#) [42-10149](#) [42-10152](#) [42-10150](#)