


Technical specification :

Rated voltage: IEC 61076-2-104	30 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment:

- 1) brown
- 2) white
- 3) blue
- 4) black
- 5) grey

Part no:	Description:	Length L:	Cable:
42-11096	SAL - 8B - RK5.1 - 2 / K1	2m	TPU, UL 20549, black, 5x0,25mm ² Cable: 781-K12500
42-11097	SAL - 8B - RK5.1 - 3 / K1	3m	
42-11098	SAL - 8B - RK5.1 - 5 / K1	5m	
42-11099	SAL - 8B - RK5.1 - 10 / K1	10m	
42-xxxxx	SAL - 8B - RK5.1 - ... / K1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 23.08.11 bcb Ä3941 data modified	dim. in mm		title: Female connector M8x1 axial, B-coding	
		date	name		
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	drawn 04.08.10	Fromm	dwg no: 42K1A240	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	appd. 04.08.10	Mankopf		
		CONEC ®		part no: see table	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-11098](#) [42-11097](#) [42-11099](#) [42-11096](#)