




Digital Visual Interface Connector PCB R/A Type

SPECIFICATIONS


Materials

Insulator: High temperature thermoplastic, UL 94V-0 white color
 Contacts: Phosphor bronze 0.38mm gold plating
 Metal Board Lock: Zinc alloy with tin plating 150µ over
 Shell: Zinc alloy with nickel plating 150µ over
 Contact Plating: Gold on contact area and tin on solder tail all with nickel underplating

Electrical

Insulation Resistance: 2000 MΩ minimum
 Contact Resistance: 20 mΩ Max. initial
 Current Rating: 1.5 Ampere
 Voltage Rating: 250V AC (rms)
 Dielectric Withstanding Voltage: 500V AC (rms)
 Temperature: 5°C ~85°C

(click on the drawing for a more detailed view)



Order Information-----

33DVI R - 24 S 0 G
 1 2 3 4 5 6

1.Series No.
 33DVI

3.No. Of Contacts
 24=24+key (digital)
 29=24+4+1 (analog)

5. Threaded Finishes
 0: #4/40 UNC hex screw
 1: #4/40 UNC threaded insert

2.Terminal Version
 R: Right angle

4.Connector Type
 S: Female

6. Contact Plating
 G: Gold flash
 A: 15µ gold
 B: 30µ gold

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

33DVIR-24S1B