



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- FRAME: STEEL; NICKEL PLATED
- FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
- RIVETED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
- CONNECTOR IS PART MARKED: DSS1XSXXB01X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND			tolerance			 dim. in mm	scale: 2:1 (5:1)	
								material: SEE NOTES	
					date	name	title: D-SUB FEMALE 9pos. CRIMP STYLE with frame and float mount		
				drawn	19.08.03	Lehmenkühler			
				appd.	19.08.03	Mickenbecker			
				norm					
	4 x c	Ä5047	16.01.2014	Lehm.	d-old		dwg no: 16K1A1002		
	2 x b	Ä3639	03.05.2010	Petker					
	a	Original							
	rev.	description	date	name			part no: DSS1XSXXB01X		
				DIN-A3 sh: 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

DSS1XSXXB01X