





P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)




see note 7



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATOR: PBT GF UL 94 V-0, GREEN
- NO CONTACTS ON POS. A1 - A3
- THREADED REAR SPACERS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- SLEEVES: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3003W3SXX99A50X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)				
							material: see notes				
								date	name	title: D-SUB COMBINATION FEMALE 3W3S with threaded rear spacer	
								drawn 17.06.13	Schmidt		
								appd. 17.06.13	Koch		
				norm		dwg no: 13K1A4345 sh: 1					
				d-old							
											
a	Original										
rev.	description	date	name			part no: 3003W3SXX99A50X					

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3003W3SXX99A50X](#)