




NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATOR: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- CAPACITANCE: 2 x 180pF ±20%
- DIELECTRIC WITHSTANDING VOLTAGE: 300 VDC
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 242A29140X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		dim. in mm
1 x b	Ä4234	26.03.12	K.H.	date	name	
a	Original			drawn	20.03.09	Sonnenberg
rev.	description	date	name	appd.	20.03.09	Fischer
				norm		
				d-old		

CONEC®

scale: 2:1 (5:1)	
material: SEE NOTES	
title: D-SUB PI FILTER FEMALE 9pos. SOLDER CUP with threaded insert	
dwg no: 24K1A1164	DIN-A3
part no: 242A29140X	
sh: 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[242A29140X](#)