





NOTES:

1. METAL SHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. HIGH POWER CONTACTS 15A: COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
PLATING TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
5. METAL BRACKETS: ZINC DIE CAST;
300µin COPPER/40-120µin NICKEL/120-200µin NICKEL
6. THREADED INSERTS:
COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. PCB-SNAPS: COPPER ALLOY; min. 20µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3,1 \pm 0,1$; PCB THICKNESS 1,6mm
8. HEXLOCKING SCREWS: STAINLESS STEEL
9. FRAME : ZINC DIE CAST; NICKEL PLATED
10. O-RING: SILICON; BLUE
11. SEALING COMPOUND: PUR; BLUE
12. P.C.B. HOLE DRILLINGS +RECOMMENDED PANEL CUT-OUT ON SHEET 2
13. RECOMMENDED TORQUE FOR MOUNTING SCREW
35Ncm (3,1in.LB)/max. 40Ncm (3,5 in.LB)
14. CONNECTOR IS PART MARKED: **6013W3SAZ59S40X CONEC ABC**



AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.



Directive 2002/95/EC RoHS compliant


THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND


				tolerance		 dim. in mm	
					date	name	
				drawn	06.12.12	Schmidt	
				appd.	06.12.12	Fischer	
				norm			
				d-old			
							
a	Original						
rev.	description	date	name				

CONEC

P.C.B. HOLE DRILLINGS (P.C.B. TOP SIDE)



RECOMMENDED PANEL CUT-OUT



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm		scale: 2:1	
								material: SEE SHEET 1	
				date	name		title: P.C.B. HOLE DRILLINGS PANEL CUT-OUT D-SUB Com. Female 90° 13W3S		
				drawn	06.12.12	Schmidt			
				appd.	06.12.12	Fischer			
				norm					
				d-old		dwg no: 15K1A1242			DIN- A3 sh: 2
a	Original					part no: SEE SHEET 1			
rev.	description	date	name						

CONEC

P.C.B. HOLE DRILLINGS
PANEL CUT-OUT
D-SUB Com. Female 90° 13W3S

DIN-A3
sh: 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

6013W3SAZ59S40X