



PTVSxS1UR-Q series

400 W Transient Voltage Suppressor

1 June 2022

Product data sheet

1. General description

400 W unidirectional Transient Voltage Suppressor (TVS) in a SOD123W small and flat lead Surface-Mounted Device (SMD) plastic package, designed for transient overvoltage protection.

2. Features and benefits

- Rated peak pulse power: $P_{PPM} = 400 \text{ W}$ (350 W for 3V3)
- Reverse standoff voltage range: $V_{RWM} = 3.3 \text{ V}$ to 64 V
- Reverse current: $I_{RM} = 0.001 \mu\text{A}$
- Very low package height: 1 mm
- Small plastic package suitable for surface-mounted design
- Qualified according to AEC-Q101 and recommended for use in automotive applications

3. Applications

- Power supply protection
- Automotive application
- Industrial application
- Power management

4. Quick reference data

Table 1. Quick reference data


Symbol	Parameter	Conditions		Min	Typ	Max	Unit
P_{PPM}	rated peak pulse power		[1] [2]	-	-	400	W
V_{RWM}	reverse standoff voltage	$T_j = 25 \text{ }^\circ\text{C}$		3.3	-	64	V

[1] In accordance with IEC 61643-321 (10/1000 μs current waveform).

[2] For PTVS3V3S1UR-Q: $P_{PPM} = 350\text{W}$.

5. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	K	cathode[1]	 CFP3 (SOD123W)	 006aaa152
2	A	anode		

[1] The marking bar indicates the cathode.

6. Ordering information

Table 3. Ordering information

Type number[1]	Package		
	Name	Description	Version
PTVSxS1UR-Q series	CFP3	plastic, surface mounted package; 2 terminals; 2.6 mm x 1.7 mm x 1 mm body	SOD123W

[1] The series consists of 35 types with reverse standoff voltages from 3.3 V to 64 V.

7. Marking

Table 4. Marking codes

Type number	Marking code	Type number	Marking code
PTVS3V3S1UR-Q	A1	PTVS20VS1UR-Q	AL
PTVS5V0S1UR-Q	A2	PTVS22VS1UR-Q	AM
PTVS6V0S1UR-Q	A3	PTVS24VS1UR-Q	AN
PTVS6V5S1UR-Q	A4	PTVS26VS1UR-Q	AP
PTVS7V0S1UR-Q	A5	PTVS28VS1UR-Q	AR
PTVS7V5S1UR-Q	A6	PTVS30VS1UR-Q	AS
PTVS8V0S1UR-Q	A7	PTVS33VS1UR-Q	AT
PTVS8V5S1UR-Q	A8	PTVS36VS1UR-Q	AU
PTVS9V0S1UR-Q	A9	PTVS40VS1UR-Q	AV
PTVS10VS1UR-Q	AA	PTVS43VS1UR-Q	AW
PTVS11VS1UR-Q	AB	PTVS45VS1UR-Q	AX
PTVS12VS1UR-Q	AC	PTVS48VS1UR-Q	AY
PTVS13VS1UR-Q	AD	PTVS51VS1UR-Q	AZ
PTVS14VS1UR-Q	AE	PTVS54VS1UR-Q	B1
PTVS15VS1UR-Q	AF	PTVS58VS1UR-Q	B2
PTVS16VS1UR-Q	AG	PTVS60VS1UR-Q	B3
PTVS17VS1UR-Q	AH	PTVS64VS1UR-Q	B4
PTVS18VS1UR-Q	AK	-	-

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
P_{PPM}	rated peak pulse power		[1] [2]	-	400	W
I_{PPM}	rated peak pulse current		[1]	-	see table 7 and 8	A
I_{FSM}	non-repetitive peak forward current	single half-sine wave; $t_p = 8.3$ ms		-	50	A
T_j	junction temperature			-	150	°C
T_{amb}	ambient temperature			-55	150	°C
T_{stg}	storage temperature			-65	150	°C
ESD maximum ratings						
V_{ESD}	electrostatic discharge voltage	IEC 61000-4-2; contact discharge	[3]	-	30	kV
		MIL-STD-883; human body model (HBM)		-	4	kV

[1] In accordance with IEC 61643-321 (10/1000 μ s current waveform).

[2] For PTVS3V3S1UR-Q: $P_{PPM} = 350$ W.

[3] Device stressed with ten non-repetitive ESD pulses.

9. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air	[1]	-	-	220	K/W
			[2]	-	-	130	K/W
			[3]	-	-	70	K/W
$R_{th(j-sp)}$	thermal resistance from junction to solder point		[4]	-	-	18	K/W

[1] Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm².

[3] Device mounted on a ceramic PCB, Al₂O₃, standard footprint.

[4] Soldering point of cathode tab.

10. Characteristics

Table 7. Characteristics per type; PTVS3V3S1UR-Q to PTVS7V0S1UR-Q

$T_j = 25^\circ\text{C}$ unless otherwise specified.



Type number PTVSxS1UR-Q	Reverse standoff voltage V_{RWM} (V)	Breakdown voltage V_{BR} (V)			Reverse leakage current I_{RM} (μ A)		Clamping voltage V_{CL} (V)	
		$I_R = 10$ mA			at V_{RWM} (V)			
	Max	Min	Typ	Max	Typ	Max	Max	I_{PPM} (A)
3V3	3.3	5.20	5.60	6.00	5	600	8.0	43.8
5V0	5.0	6.40	6.70	7.00	5	400	9.2	43.5
6V0	6.0	6.67	7.02	7.37	5	400	10.3	38.8
6V5	6.5	7.22	7.60	7.98	5	250	11.2	35.7
7V0	7.0	7.78	8.20	8.60	3	100	12.0	33.3

Table 8. Characteristics per type; PTVS7V5S1UR-Q to PTVS64VS1UR-Q

$T_j = 25^\circ\text{C}$ unless otherwise specified.

Type number PTVSxS1UR-Q	Reverse standoff voltage V_{RWM} (V)	Breakdown voltage V_{BR} (V)			Reverse leakage current I_{RM} (μA)		Clamping voltage V_{CL} (V)	
		$I_{\text{R}} = 1 \text{ mA}$			at V_{RWM} (V)			
	Max	Min	Typ	Max	Typ	Max	Max	I_{PPM} (A)
7V5	7.5	8.33	8.77	9.21	0.2	50	12.9	31.0
8V0	8.0	8.89	9.36	9.83	0.03	25	13.6	29.4
8V5	8.5	9.44	9.92	10.40	0.01	10	14.4	27.8
9V0	9.0	10.00	10.55	11.10	0.005	5	15.4	26.0
10V	10	11.10	11.70	12.30	0.005	2.5	17.0	23.5
11V	11	12.20	12.85	13.50	0.005	2.5	18.2	22.0
12V	12	13.30	14.00	14.70	0.005	2.5	19.9	20.1
13V	13	14.40	15.15	15.90	0.001	0.1	21.5	18.6
14V	14	15.60	16.40	17.20	0.001	0.1	23.2	17.2
15V	15	16.70	17.60	18.50	0.001	0.1	24.4	16.4
16V	16	17.80	18.75	19.70	0.001	0.1	26.0	15.4
17V	17	18.90	19.90	20.90	0.001	0.1	27.6	14.5
18V	18	20.00	21.00	22.10	0.001	0.1	29.2	13.7
20V	20	22.20	23.35	24.50	0.001	0.1	32.4	12.3
22V	22	24.40	25.60	26.90	0.001	0.1	35.5	11.3
24V	24	26.70	28.10	29.50	0.001	0.1	38.9	10.3
26V	26	28.90	30.40	31.90	0.001	0.1	42.1	9.5
28V	28	31.10	32.80	34.40	0.001	0.1	45.4	8.8
30V	30	33.30	35.10	36.80	0.001	0.1	48.4	8.3
33V	33	36.70	38.70	40.60	0.001	0.1	53.3	7.5
36V	36	40.00	42.10	44.20	0.001	0.1	58.1	6.9
40V	40	44.40	46.80	49.10	0.001	0.1	64.5	6.2
43V	43	47.80	50.30	52.80	0.001	0.1	69.4	5.8
45V	45	50.00	52.65	55.30	0.001	0.1	72.7	5.5

Type number PTVSxS1UR-Q	Reverse standoff voltage V _{RWM} (V)	Breakdown voltage V _{BR} (V)			Reverse leakage current I _{RM} (μA)		Clamping voltage V _{CL} (V)	
		I _R = 1 mA			at V _{RWM} (V)			
	Max	Min	Typ	Max	Typ	Max	Max	I _{PPM} (A)
48V	48	53.30	56.10	58.90	0.001	0.1	77.4	5.2
51V	51	56.70	59.70	62.70	0.001	0.1	82.4	4.9
54V	54	60.00	63.15	66.30	0.001	0.1	87.1	4.6
58V	58	64.40	67.80	71.20	0.001	0.1	93.6	4.3
60V	60	66.70	70.20	73.70	0.001	0.1	96.8	4.1
64V	64	71.10	74.85	78.60	0.001	0.1	103.0	3.9



11. Test information

Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - *Stress test qualification for discrete semiconductors*, and is suitable for use in automotive applications.

12. Package outline




Fig. 3. Package outline CFP3 (SOD123W)

13. Soldering




Fig. 4. Reflow soldering footprint for CFP3 (SOD123W)




Fig. 5. Wave soldering footprint for CFP3 (SOD123W)

14. Revision history

Table 9. Revision history

Data sheet ID	Release date	Data sheet status	Change notice	Supersedes
PTVSxS1UR-Q_SER v.1	20220601	Product data sheet	-	-

15. Legal information

Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <https://www.nexperia.com>.

Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or

equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description.....	1
2. Features and benefits.....	1
3. Applications.....	1
4. Quick reference data.....	1
5. Pinning information.....	2
6. Ordering information.....	2
7. Marking.....	2
8. Limiting values.....	3
9. Thermal characteristics.....	3
10. Characteristics.....	4
11. Test information.....	5
12. Package outline.....	6
13. Soldering.....	7
14. Revision history.....	9
15. Legal information.....	10

© Nexperia B.V. 2022. All rights reserved

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 1 June 2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nexperia:](#)

[PTVS13VS1UR-QX](#) [PTVS14VS1UR-QX](#) [PTVS15VS1UR-QX](#) [PTVS17VS1UR-QX](#) [PTVS24VS1UR-QX](#)
[PTVS26VS1UR-QX](#) [PTVS28VS1UR-QX](#) [PTVS30VS1UR-QX](#) [PTVS33VS1UR-QX](#) [PTVS36VS1UR-QX](#)
[PTVS54VS1UR-QX](#) [PTVS58VS1UR-QX](#) [PTVS64VS1UR-QX](#) [PTVS6V0S1UR-QX](#)