

Starting/running torque from 30 and 37.5 mN.m 3.5 Watts Part number 82520014



- Constant speed, dependent on supply frequency
- Direction of rotation controlled by dephasing capacitor
- Sintered bearing lubricated for life
- Silent operation
- UL, CSA (classe B)

Part numbers

	Type	Type	Voltages/Frequencies
82 520 014	3.5 Watts	82 520 0	230-240 V 50 Hz

Specifications


Base speed of motor (rpm)	250
Absorbed power (W)	3.5
Usable Power (W)	0,98
Starting/running torque (mNm)	37,5
Stall torque (mNm)	42
Temperature rise (°C)	55
Ambient temperature (°C)	-10+75
Maximum inertial load that can be moved (g.cm ²)	33
Number of offload starts	
Insulation resistance (MΩ)	75x10 ³
Breakdown voltage (V-50 Hz)	1800 -1 sec.
Weight (g)	210
Wires length mm (approximately)	250
Protection rating	IP40

Accessories

Voltages/Frequencies	μF	V AC	Code
Capacitors motor 82 520 0	Condensateur		
230-240 V - 50 Hz	0,1 ± 10 %	500	26 231 941
115 V 60 Hz	0,33 ± 10 %	240	26 231 801
24 V - 50 Hz	8,2 ± 10 %	63	26 231 711

Dimensions (mm)


82 520 0



N°	Legend
1	2 oblong fixing holes 3.5 wide

Connections

In parallel
Motors 82 520 0 - 82 520 4



N°	Legend
1	SA : Clockwise
2	SI : Anti-clockwise

Product adaptations

- 
- Different voltages available
 - Pinion on output shaft
 - Special output shafts
 - Special supply voltages
 - Special cable lengths
 - Special output bearings
 - Special mounting plate
 - Special connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crouzet:

82520014