









P.C.B. HOLE DRILLINGS
 (P.C.B. TOP SIDE)



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: Ø3.1 ± 0.1; PCB THICKNESS 2,3mm
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: DSH1XSRAA19X CONEC ABC



Directive 2002/95/EC
 „RoHS“
 Compliant

THIS DRAWING MAY NOT BE COPIED OR
 REPRODUCED IN ANY WAY, AND MAY NOT
 BE PASSED ON TO A THIRD PARTY WITHOUT
 WRITTEN PERMISSION.
 OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance ISO 2768-m		 dim. in mm
					date	
				drawn	23.11.10	Henneboel
				appd.	23.11.10	Koch
				norm		
				d-old		
a	Origin					
rev.	description	date	name			

scale:	2:1 (5:1)		
material:	SEE NOTES		
title:			
D-SUB HD FEMALE			
15pos. SOLDER PIN STRAIGHT			
with threaded spacer clip			
dwg no:		Inventor 10	DIN-A3
16K1A2742		sh: 1	
part no:		DSH1XSRAA19X	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[DSH1XSRAA19X](#)