









P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



NOTES:

1. METALSHIELDS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
4. THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
7. CONNECTOR IS PART MARKED: DSH2XSRAA19X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	finish:				tolerance		 dim. in mm	scale:		2:1 (5:1)		
								material:		SEE NOTES		
						date	name		title: D-SUB HD FEMALE 26pos. SOLDER PIN STRAIGHT threaded spacer clip			
						drawn	22.11.10 Henneboel					
						appd.	22.11.10 Fischer					
						norm						
						d-old		dwg no:		DIN- A3 sh: 1		
	1 x b	Ä3946	18.03.2011	K.H.			16K1A2740					
	a	Original										
	rev.	description	date	name			part no:		DSH2XSRAA19X			

DIN-
A3
sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[DSH2XSRAA19X](#)